

Chipsmall Limited consists of a professional team with an average of over 10 year of expertise in the distribution of electronic components. Based in Hongkong, we have already established firm and mutual-benefit business relationships with customers from, Europe, America and south Asia, supplying obsolete and hard-to-find components to meet their specific needs.

With the principle of "Quality Parts, Customers Priority, Honest Operation, and Considerate Service", our business mainly focus on the distribution of electronic components. Line cards we deal with include Microchip, ALPS, ROHM, Xilinx, Pulse, ON, Everlight and Freescale. Main products comprise IC, Modules, Potentiometer, IC Socket, Relay, Connector. Our parts cover such applications as commercial, industrial, and automotives areas.

We are looking forward to setting up business relationship with you and hope to provide you with the best service and solution. Let us make a better world for our industry!



## Contact us

Tel: +86-755-8981 8866 Fax: +86-755-8427 6832

Email & Skype: info@chipsmall.com Web: www.chipsmall.com

Address: A1208, Overseas Decoration Building, #122 Zhenhua RD., Futian, Shenzhen, China









Microscope Lighting/Digital Options

18743

Old item no.: 18743



## LED RING LIGHT HO DIMMING

ESD-Safe, Dimmable LED-High Output Ring Light maximizes light output at a greater working distance. Its 80 high-output LEDs draw on 18-watts of energy while producing up to 5800 footcandles at 4.5" working distance. The LEDs are distributed among 2 concentric rings of lights (each containing 40 LEDs) with individual quadrant controls. A 50,000 hour lumen maintenance (lamp life) and 6000°K color temperature make this an ideal lightsource for the inspection of surface cracks and defects, welds, lead-free solder joints, flux residues and hairline stress cracks as well as a suitable replacement for traditional 150W Fiber Optic Illuminators. Three mounting points enable the Dimmable LED-High Output Ring Light to be safety wired to the scope body. This, along with a new permanently affixed power cord, provides additional assurance that the ring light will remain securely attached



## Dimensions

Net weight (kg)

Λ