



Chipsmall Limited consists of a professional team with an average of over 10 year of expertise in the distribution of electronic components. Based in Hongkong, we have already established firm and mutual-benefit business relationships with customers from,Europe,America and south Asia,supplying obsolete and hard-to-find components to meet their specific needs.

With the principle of “Quality Parts,Customers Priority,Honest Operation,and Considerate Service”,our business mainly focus on the distribution of electronic components. Line cards we deal with include Microchip,ALPS,ROHM,Xilinx,Pulse,ON,Everlight and Freescale. Main products comprise IC,Modules,Potentiometer,IC Socket,Relay,Connector.Our parts cover such applications as commercial,industrial, and automotives areas.

We are looking forward to setting up business relationship with you and hope to provide you with the best service and solution. Let us make a better world for our industry!



Contact us

Tel: +86-755-8981 8866 Fax: +86-755-8427 6832

Email & Skype: info@chipsmall.com Web: www.chipsmall.com

Address: A1208, Overseas Decoration Building, #122 Zhenhua RD., Futian, Shenzhen, China





注記:

- 1. 本ツールはダイナミックD-3000シリーズコネクタ用引抜工具である。
- 2. 適用コネクタ名称: ダイナミックD-3000シリーズコネクタ
- 3. 適用製品型番:

- a) 端子型番:
- | | |
|-----------------------------------|-----------------------------------|
| <input type="checkbox"/> 175196- | <input type="checkbox"/> 175286- |
| <input type="checkbox"/> -175194- | <input type="checkbox"/> -175284- |
| <input type="checkbox"/> -175195- | <input type="checkbox"/> -175285- |
| <input type="checkbox"/> -175216- | <input type="checkbox"/> -175287- |
| <input type="checkbox"/> -175217- | <input type="checkbox"/> -175288- |
| <input type="checkbox"/> -175218- | <input type="checkbox"/> -175289- |
| <input type="checkbox"/> -353715- | <input type="checkbox"/> -353716- |
| <input type="checkbox"/> -353717- | <input type="checkbox"/> -353718- |
| <input type="checkbox"/> -917484- | <input type="checkbox"/> -917485- |
| <input type="checkbox"/> -917511- | <input type="checkbox"/> -917512- |

- b) ハウジング型番:
- | | |
|-----------------------------------|-----------------------------------|
| <input type="checkbox"/> -175362- | <input type="checkbox"/> -175363- |
| <input type="checkbox"/> -177648- | <input type="checkbox"/> -178127- |
| <input type="checkbox"/> -178128- | <input type="checkbox"/> -178129- |
| <input type="checkbox"/> -178288- | <input type="checkbox"/> -178289- |
| <input type="checkbox"/> -178214- | <input type="checkbox"/> -178964- |
| <input type="checkbox"/> -178802- | <input type="checkbox"/> -178803- |

4. 取扱説明書番号: 411-5726

5. 重量: 約 22g

NOTES:



- 1. THIS EXTRACTION TOOL IS SPECIFICALLY DESIGNED TO EXTRACT THE CONTACT FOR DYNAMIC D-3000 SERIES CONNECTOR.
- 2. CONNECTRO NAME : DYNAMIC D-3000 SERIES CONNECTOR
- 3. APPLICABLE PRODUCTS:

- a) TERMINAL P/N:
- | | |
|-----------------------------------|-----------------------------------|
| <input type="checkbox"/> 175196- | <input type="checkbox"/> 175286- |
| <input type="checkbox"/> -175194- | <input type="checkbox"/> -175284- |
| <input type="checkbox"/> -175195- | <input type="checkbox"/> -175285- |
| <input type="checkbox"/> -175216- | <input type="checkbox"/> -175287- |
| <input type="checkbox"/> -175217- | <input type="checkbox"/> -175288- |
| <input type="checkbox"/> -175218- | <input type="checkbox"/> -175289- |
| <input type="checkbox"/> -353715- | <input type="checkbox"/> -353716- |
| <input type="checkbox"/> -353717- | <input type="checkbox"/> -353718- |
| <input type="checkbox"/> -917484- | <input type="checkbox"/> -917485- |
| <input type="checkbox"/> -917511- | <input type="checkbox"/> -917512- |

- b) HOUSING P/N:
- | | |
|-----------------------------------|-----------------------------------|
| <input type="checkbox"/> -175362- | <input type="checkbox"/> -175363- |
| <input type="checkbox"/> -177648- | <input type="checkbox"/> -178127- |
| <input type="checkbox"/> -178128- | <input type="checkbox"/> -178129- |
| <input type="checkbox"/> -178288- | <input type="checkbox"/> -178289- |
| <input type="checkbox"/> -178214- | <input type="checkbox"/> -178964- |
| <input type="checkbox"/> -178802- | <input type="checkbox"/> -178803- |

4. INSTRUCTION SHEET NO.: 411-5726

5. WEIGHT : 22g APPROX.



PRINT DIST 単位: 概 DIMENSIONS IN MM. DO NOT SCALE PRINT

		TE TE Connectivity	
名称 (NAME)		EXTRACTION TOOL FOR DYNAMIC D-3	
ダイナミックD-3用引抜工具			
絶縁電線断面積 (WIRE RANGE)	被覆外径 (INSULATION DIA.)	公差	SIZE
mm ² (AWG)	mm	10以下 ±0.2	A3
材料 (MATERIAL)	仕上 (FINISH)	10を超え 30以下 ±0.25	LOC
		30を超え 100以下 ±0.3	J
DR. 16 JUN '95	DE. 4 JUL '95	角 度 ±0.3	番号 (NO.)
J. SEKI			234168-1
CHK. 4 JUL '95	APP. 16 SEP '95	尺度 (SCALE)	REV. A1
J. SEKI		1-1	SHEET 1 OF 1

A1	REVISED PER ECO-11-005294	RK	HMR	07 APR 11
LTR	変更 (REVISION RECORD)	DR.	CHK.	DATE