



Chipsmall Limited consists of a professional team with an average of over 10 year of expertise in the distribution of electronic components. Based in Hongkong, we have already established firm and mutual-benefit business relationships with customers from,Europe,America and south Asia,supplying obsolete and hard-to-find components to meet their specific needs.

With the principle of "Quality Parts,Customers Priority,Honest Operation,and Considerate Service",our business mainly focus on the distribution of electronic components. Line cards we deal with include Microchip,ALPS,ROHM,Xilinx,Pulse,ON,Everlight and Freescale. Main products comprise IC,Modules,Potentiometer,IC Socket,Relay,Connector.Our parts cover such applications as commercial,industrial, and automotives areas.

We are looking forward to setting up business relationship with you and hope to provide you with the best service and solution. Let us make a better world for our industry!



Contact us

Tel: +86-755-8981 8866 Fax: +86-755-8427 6832

Email & Skype: info@chipsmall.com Web: www.chipsmall.com

Address: A1208, Overseas Decoration Building, #122 Zhenhua RD., Futian, Shenzhen, China



Aven Inc.
 4595 Platt Rd.
 Ann Arbor, MI 48108
Phone: 734.973.0099
Email: info@aventools.com • **Web Address:** www.aventools.com

All Categories > Fluorescent Ring Lights > Sirius Quartz Halogen Task Lights > Micro Zoom Video Inspection Systems - VIS-6000 > Item # 26700-102-00

Item # 26700-102-00, Micro Zoom Video Inspection System



[larger image](#)

VIS 6000 with Zoom 6000 lens, 0.5x adapter tube and auxiliary lens, miniVue Camera and 150 watt FOI with Ring Light. Mounted on the Ergo Stand with 11" x 18" base. With our miniVue camera, images can be saved directly onto a SD Card.

[Applications](#) · [Specifications](#) · [0.5x Adapter](#) · [1x Adapter](#) · [2x Adapter](#) · [5x Adapter](#)

Applications

Inspection of a wide range of objects such as integrated circuits, solder joints, surface analysis, quality control and laboratory inspection.

Specifications

Stand	Ergo Stand
Customization	A variety of adapters & auxiliary lens, cameras, lighting options, video capture cards, and stands are available to provide a custom solution.
Magnification Range	2x to 2735x possible.
High Accuracy Measurement	Detented Lenses are available for high accuracy measurements.
12x Zoom Lenses	For customers requiring the highest combination of zoom range and resolution.
Magnification (0.5x Adapter)	<ul style="list-style-type: none"> ● Lens Attachment 0.25x : 5x to 33x ● Lens Attachment 0.50x : 10x to 67x ● Lens Attachment 0.75x : 16x to 100x ● Lens Attachment None : 21x to 133x ● Lens Attachment 1.50x : 31x to 200x ● Lens Attachment 2.00x : 41x to 267x
Weight	35 lb

0.5x Adapter

Field of View (0.5x Adapter)	<ul style="list-style-type: none"> ● Lens Attachment 0.25x : 64.68 to 10.64 ● Lens Attachment 0.50x : 34.32 to 5.32 ● Lens Attachment 0.75x : 17.16 to 2.67 ● Lens Attachment None : 17.16 to 2.67 ● Lens Attachment 1.50x : 11.43 to 1.78
-------------------------------------	--

- **Lens Attachment 2.00x** : 8.58 to 1.33

1x Adapter

Magnification (1x Adapter)	<ul style="list-style-type: none"> ● Lens Attachment 0.25x : 10x to 67x ● Lens Attachment 0.50x : 21x to 133x ● Lens Attachment 0.75x : 31x to 200x ● Lens Attachment None : 41x to 267x ● Lens Attachment 1.50x : 62x to 400x ● Lens Attachment 2.00x : 83x to 531x
Field of View (1x Adapter)	<ul style="list-style-type: none"> ● Lens Attachment 0.25x : 34.32 to 5.32 ● Lens Attachment 0.50x : 17.16 to 2.67 ● Lens Attachment 0.75x : 8.58 to 1.33 ● Lens Attachment None : 8.58 to 1.33 ● Lens Attachment 1.50x : 5.72 to 0.89 ● Lens Attachment 2.00x : 4.29 to 0.67

2x Adapter

Magnification (2x Adapter)	<ul style="list-style-type: none"> ● Lens Attachment 0.25x : 21x to 134x ● Lens Attachment 0.50x : 41x to 267x ● Lens Attachment 0.75x : 62x to 400x ● Lens Attachment None : 83x to 531x ● Lens Attachment 1.50x : 124x to 808x ● Lens Attachment 2.00x : 165x to 1078x
Field of View (2x Adapter)	<ul style="list-style-type: none"> ● Lens Attachment 0.25x : 17.16 to 2.66 ● Lens Attachment 0.50x : 8.58 to 1.33 ● Lens Attachment 0.75x : 4.29 to 0.67 ● Lens Attachment None : 4.29 to 0.67 ● Lens Attachment 1.50x : 2.86 to 0.44 ● Lens Attachment 2.00x : 2.15 to 0.33

5x Adapter

Magnification (5x Adapter)	<ul style="list-style-type: none"> ● Lens Attachment 0.25x : 52x to 329x ● Lens Attachment 0.50x : 104x to 671x ● Lens Attachment 0.75x : 155x to 1016x ● Lens Attachment None : 207x to 1317x ● Lens Attachment 1.50x : 312x to 1976x ● Lens Attachment 2.00x : 413x to 2735x
	<ul style="list-style-type: none"> ● Lens Attachment 0.25x : 6.88 to 1.08 ● Lens Attachment 0.50x : 3.43 to 0.53

Field of View (5x Adapter)

- **Lens Attachment 0.75x** : 1.72 to 0.27
- **Lens Attachment 0.75x** : 1.72 to 0.27
- **Lens Attachment 1.50x** : 1.14 to 0.18
- **Lens Attachment 2.00x** : 0.86 to 0.13

[Print](#) [Back](#)