



Chipsmall Limited consists of a professional team with an average of over 10 year of expertise in the distribution of electronic components. Based in Hongkong, we have already established firm and mutual-benefit business relationships with customers from,Europe,America and south Asia,supplying obsolete and hard-to-find components to meet their specific needs.

With the principle of “Quality Parts,Customers Priority,Honest Operation,and Considerate Service”,our business mainly focus on the distribution of electronic components. Line cards we deal with include Microchip,ALPS,ROHM,Xilinx,Pulse,ON,Everlight and Freescale. Main products comprise IC,Modules,Potentiometer,IC Socket,Relay,Connector.Our parts cover such applications as commercial,industrial, and automotives areas.

We are looking forward to setting up business relationship with you and hope to provide you with the best service and solution. Let us make a better world for our industry!



Contact us

Tel: +86-755-8981 8866 Fax: +86-755-8427 6832

Email & Skype: info@chipsmall.com Web: www.chipsmall.com

Address: A1208, Overseas Decoration Building, #122 Zhenhua RD., Futian, Shenzhen, China





Note: 0.5x Auxiliary Lens cannot be used on this SPZH series body with stand P, PF, T and TL

SPZH-135 Stereo Zoom Microscope with DBL Arm Boom, EARM, LED FOI illumination

The ideal scope for a wide range of investigative/inspection applications, Aven's dynamic new microscope SPZH-135 extends the boundaries of stereo zoom microscopy, employing standard 15X eyepieces to achieve 21x to 135x continuous zoom magnification all the while providing a constant working distance of 3.3" (84mm). The versatility of the SPZH-135 can be realized by adding an optional 0.5x auxiliary lens for an extended working distance of 5.31" (135mm) while still providing high magnification in the range of 10.5x to 67.5x. Replacing the standard 15X eyepieces with our DHW20X eyepieces enhances the magnification range of this dynamic new microscope further – 28X to 180X. Having eyepieces set at a 45 degree angle, the adjustable interpupillary distance between eyepieces of 1.96" (50mm) to 2.91" (74mm) means they can be set to the comfort level of any user. Mounted on a double arm boom stand with E-ARM focus mount and having illumination provided by a High Output LED fiber optic illuminator and ring light makes this system ideal for virtually any investigative or inspection application.

Aven microscopes reflect the clear differences of Japanese-engineered instruments designed and manufactured to industry-leading standards. High-grade optical glass and a straight light path provide maximum clarity and undistorted viewing.

Features

- Total Magnification of 21X to 135X at 3.3" (84mm) working distance, Max 180X with 20X eyepieces
- Standard High Eye Point wide field 15x eyepieces at 45 degrees for comfortable viewing even for operators with eyeglasses
- Diopter adjustment on both eyepiece tubes
- Adjustable Interpupillary Distance of 1.96" (50mm) to 2.91" (74MM) accommodates any operator
- Mounted in an E-ARM focus mount attached to a Double Arm boom stand w/ball bearing glides
- High Output LED fiber optic illuminator and ring light provide clear illumination for imaging
- Optional equipment 0.5X Auxiliary lens and 20X eyepieces available

BODY	Binocular
EYEPIECE	15x Wide Field inclined at 45 Degree
MAGNIFICATION	21x to 135x, Max 180x with 20x eyepieces
WORKING DISTANCE	84mm (3.3")
INTERPUPILLARY DISTANCE	50mm(1.96") to 74mm (2.91")
DIOPTER ADJUSTMENT	+5.6D-7.2D on both eyepieces
OPTICAL SYSTEM	Greenough
STAND TYPE	Double Arm w/ball bearing glides
BASE DIMENSIONS/WEIGHT	285mm x 260mm x 18mm/11.25"x10.25"x .71" 17.35 kg/38lbs
POLE/TRACK HEIGHT	380mm/14.96"
HORIZONTAL ARM	384mm/15.1"
FOCUS MOUNT	E-ARM - Course and fine focus
ILLUMINATION	LED FOI w/FO ring light
ACCESSORIES INCLUDED	Dust Cover (Rubber Eye Guards), Tension Control Pin
OPTIONAL ACCESSORIES	20x Eyepieces, Protective Lens Cover 0.5X Auxiliary lens
WEIGHT	55 lbs
PACKAGE CONTENTS	SPZH-135 Body; Dble Arm Boom 26800B-534; E-ARM Focus Mount 26800B-518; LED Fiber Optic Illuminator 26200A-300; Fiber Optic Ring light 26200A-402; Ring light adapter 26800B-460

26800B-352

SPZH-135 Stereo Zoom Microscope w/ DBL Arm Boom, EARM, LED FOI illumination