



Chipsmall Limited consists of a professional team with an average of over 10 year of expertise in the distribution of electronic components. Based in Hongkong, we have already established firm and mutual-benefit business relationships with customers from,Europe,America and south Asia,supplying obsolete and hard-to-find components to meet their specific needs.

With the principle of “Quality Parts,Customers Priority,Honest Operation,and Considerate Service”,our business mainly focus on the distribution of electronic components. Line cards we deal with include Microchip,ALPS,ROHM,Xilinx,Pulse,ON,Everlight and Freescale. Main products comprise IC,Modules,Potentiometer,IC Socket,Relay,Connector.Our parts cover such applications as commercial,industrial, and automotives areas.

We are looking forward to setting up business relationship with you and hope to provide you with the best service and solution. Let us make a better world for our industry!



Contact us

Tel: +86-755-8981 8866 Fax: +86-755-8427 6832

Email & Skype: info@chipsmall.com Web: www.chipsmall.com

Address: A1208, Overseas Decoration Building, #122 Zhenhua RD., Futian, Shenzhen, China



NEW



Microscope w/Integrated LED Ring Light

One-piece system adds convenience and peace of mind.

This inspection and laboratory microscope offers a best-in-class zoom ratio with sharp 3D images, wide field of view and large working distance. As another distinctive advantage, the ring light is a secure part of the focus mount. Making the illumination unit an integral component, rather than a screw-on accessory, eliminates the danger of damage from a loosened ring light dropping on products being examined.

Features

- Superior optics and reliable mechanical components
- Magnification: 6.7x to 50x
- Magnification range with optional lenses: 6.7x to 200x
- High eye point of 17mm for comfortable viewing, even for operators with eye glasses
- Large zoom ratio gives this microscope exceptional versatility
- Multi-coated optical components, free from chromatic and spherical aberration
- Crystal clear high resolution images
- Double arm boom stand allows positioning of the microscope over large areas
- Tilt able arbor enables you to angle the microscope for maximum comfort and viewing
- Integrated 60 LED Ring Light with dimmer

ILLUMINATION	60 LED Ring Light, 56000K White, 35,000 LUX
LIGHTING CONTROL	Variable
BODY	Binocular
OBJECTIVE LENS	0.67x to 5.0x
MAGNIFICATION	6.7x to 50x
EYEPIECE	10x Wide Field (FN:23), 45° Inclined
INTERPUPILARY DISTANCE	52 to 75mm
DIOPTER ADJUSTMENT	+/- 7.2 D in both eyepiece tube
OPTICAL SYSTEM	Greenough
STAND TYPE	Double Arm Boom Stand with Tilt able Arbor
BASE DIMENSIONS	285 x 260 x 18mm
POLE/TRACK HEIGHT	380mm; Extension Post: 225mm
ACCESSORIES INCLUDED	Dust Cover Rubber Eye Guards Tension Control Pin
WEIGHT	75lbs
PACKAGE CONTENTS	Double Arm Boom Stand with arbor 26800B-535; Integrated LED Ring Light with Focus Mount 26800B-535; SPZT Stereo Zoom Binocular Body

26800B-369

SPZ-50 Stereo Zoom Microscope w/ Integrated LED Ring Light on DABS