



Chipsmall Limited consists of a professional team with an average of over 10 year of expertise in the distribution of electronic components. Based in Hongkong, we have already established firm and mutual-benefit business relationships with customers from,Europe,America and south Asia,supplying obsolete and hard-to-find components to meet their specific needs.

With the principle of “Quality Parts,Customers Priority,Honest Operation,and Considerate Service”,our business mainly focus on the distribution of electronic components. Line cards we deal with include Microchip,ALPS,ROHM,Xilinx,Pulse,ON,Everlight and Freescale. Main products comprise IC,Modules,Potentiometer,IC Socket,Relay,Connector.Our parts cover such applications as commercial,industrial, and automotives areas.

We are looking forward to setting up business relationship with you and hope to provide you with the best service and solution. Let us make a better world for our industry!



Contact us

Tel: +86-755-8981 8866 Fax: +86-755-8427 6832

Email & Skype: info@chipsmall.com Web: www.chipsmall.com

Address: A1208, Overseas Decoration Building, #122 Zhenhua RD., Futian, Shenzhen, China



One Part Free Flowing Syntactic Foam Powder

FREE FLOWING SYNTACTIC FOAM POWDER



Eccostock FFP is a one-part, epoxy-based, free-flowing powder. It cures at elevated temperatures to a rigid, non-burning syntactic foam. It is extremely light weight and provides physical support as well as thermal insulation without increasing the weight or dielectric constant. Eccostock FFP exhibits minimum shrinkage during cure, exerting minimum stress on delicate components. Cured material can be easily removed with tools enabling access to repair or replace components. Since cured Eccostock FFP is porous, application of an epoxy coating will reduce moisture absorption.

FEATURES AND BENEFITS

- Low cost
- Low shrinkage during cure
- No mixing required and easy to use as it is a one part curing system

MARKETS

- Commercial Telecom
- Security and Defense

SPECIFICATIONS

TYPICAL PROPERTIES	ECCOSTOCK FFP
Temperature Range °C (°F)	-65 to 175 (-85 to 347)
Density, g/cc	0.24
Compression Strength kPa (psi)	1000 (150)
Dielectric Constant @ 8.6 GHz	1.25
Loss Tangent @ 8.6 GHz	0.005
Dielectric Strength, volts/mil	64
Thermal Conductivity W/mK	0.051
Volume Resistivity, ohm-cm	3.49×10^{11}

Data for design engineer guidance only. Observed performance varies in application. Engineers are reminded to test the material in application.

APPLICATIONS

- Eccostock FFP is designed to infiltrate densely populated electronic packages, readily filling available volumes around components. It been used to stabilize crystal oscillators as well as other delicate components that need to be held in place or thermally protected.
- Eccostock FFP has also found its way into machinery operating in high vibration environments to keep electrical components from shaking apart.
- Low shrinkage during cure makes
- Eccostock FFP excellent for encapsulation applications.

AVAILABILITY

- Eccostock FFP is readily available in pints, quarts, gallons, and 5 gallon containers. Pint and quart containers are also available in squeeze bottles for ease of application.

INSTRUCTIONS FOR USE

- Refer to the MSDS for full safety information before opening the container. Measures should be taken to avoid any contact with the skin and eyes, and a dust mask or respirator should be used to avoid inhaling the product.
- Mix the Eccostock FFP in the shipping container by lightly tumbling or shaking before use, as some components may separate during shipping and storage.
- In a well ventilated area, carefully pour the Eccostock FFP from a small paper cup or dispense from a squeeze bottle into the device being filled.
- Light to moderate vibration is recommended to maximize packing of the material.
- Eccostock FFP bonds well to itself and most other substrates. Mold release wax is recommended in applications where removal from a mold is necessary.
- Shelf life is 6 months if stored in a cool dry place out of direct sunlight at 21 °C (70 °F).
- Elevated temperature curing is required. Select one of the following recommended curing times and temperatures:

Cure Times and Temperatures

24 hours at 100°C (212°F)

4 hours at 120°C (248°F)

2 hours at 150°C (302°F)