



Chipsmall Limited consists of a professional team with an average of over 10 year of expertise in the distribution of electronic components. Based in Hongkong, we have already established firm and mutual-benefit business relationships with customers from,Europe,America and south Asia,supplying obsolete and hard-to-find components to meet their specific needs.

With the principle of “Quality Parts,Customers Priority,Honest Operation,and Considerate Service”,our business mainly focus on the distribution of electronic components. Line cards we deal with include Microchip,ALPS,ROHM,Xilinx,Pulse,ON,Everlight and Freescale. Main products comprise IC,Modules,Potentiometer,IC Socket,Relay,Connector.Our parts cover such applications as commercial,industrial, and automotives areas.

We are looking forward to setting up business relationship with you and hope to provide you with the best service and solution. Let us make a better world for our industry!



Contact us

Tel: +86-755-8981 8866 Fax: +86-755-8427 6832

Email & Skype: info@chipsmall.com Web: www.chipsmall.com

Address: A1208, Overseas Decoration Building, #122 Zhenhua RD., Futian, Shenzhen, China





Description

- Dissipative Yellow Bottle with swan neck spout
- Promotes ESD control awareness
- Used to hold water for wetting sponges at soldering stations, to hold cleaning agents or similar liquids
- Simply squeeze the bottle to release some contents through the spout.
- No Migratory Additives - reduces the chance for contamination from the bottle
- LDPE durAstatic bottles are dissipative; electrostatic charges are removed to ground when handled by a grounded operator or in contact with ESD worksurface
- Highly visible with ESD protective symbol, allowing people to immediately know the bottle is ESD protective
- Available in 8 or 16 ounce Bottle

Specifications

Bottle volume resistance 1×10^4 to $< 1 \times 10^{11}$ ohms per ANSI/ESD STM11.12
 Meets ANSI/ESD S20.20, EN 61340-5-1, ANSI/ESD S541 and EN 61340-5-3

9"
(228mm)



5 1/2"
(140mm)

35436

7 3/4"
(197mm)



4 1/4"
(108mm)

35359

35359

- Material = LDPE
- Size = 8 oz. (240mL)
- Base Diameter = 2-1/4" (57mm)
- Neck Size = 28-400
- Height = 7-3/4" (197mm)

35436

- Material = LDPE
- Size = 16 oz. (480mL)
- Base Diameter = 2.9" (74mm)
- Neck Size = 28-400
- Height = 9" (228mm)

35359	8 oz. (240mL) Bottle, Dissipative LPDE, Yellow
35436	16 oz. (480mL) Bottle, Dissipative LPDE, Yellow

"It should be understood that any object, item, material or person could be a source of static electricity in the work environment. Removal of unnecessary nonconductors, replacing nonconductive materials with dissipative or conductive materials and grounding all conductors are the principle methods of controlling static electricity in the workplace, regardless of the activity." [ESD Handbook ESD TR20.20 section 2.4 Sources of Static Electricity]

If not otherwise noted, tolerances ± 10%
 Specifications and procedures subject to change without notice.

durAstatic Dissipative Wash Bottles

MENDA

3651 WALNUT AVE., CHINO, CA 91710
 PHONE: (909) 627-2453
 WEBSITE: MendaPump.com

DRAWING NUMBER
35359

DATE:
May
2016