



Chipsmall Limited consists of a professional team with an average of over 10 year of expertise in the distribution of electronic components. Based in Hongkong, we have already established firm and mutual-benefit business relationships with customers from,Europe,America and south Asia,supplying obsolete and hard-to-find components to meet their specific needs.

With the principle of “Quality Parts,Customers Priority,Honest Operation,and Considerate Service”,our business mainly focus on the distribution of electronic components. Line cards we deal with include Microchip,ALPS,ROHM,Xilinx,Pulse,ON,Everlight and Freescale. Main products comprise IC,Modules,Potentiometer,IC Socket,Relay,Connector.Our parts cover such applications as commercial,industrial, and automotives areas.

We are looking forward to setting up business relationship with you and hope to provide you with the best service and solution. Let us make a better world for our industry!



## Contact us

Tel: +86-755-8981 8866 Fax: +86-755-8427 6832

Email & Skype: info@chipsmall.com Web: www.chipsmall.com

Address: A1208, Overseas Decoration Building, #122 Zhenhua RD., Futian, Shenzhen, China



## Natural HDPE Bottles

- High density polyethylene, suitable for many solvents
- Square shape for stability
- Wide opening for easy filling
- Translucent, white finish allows easy viewing of contents
- Custom imprinting available
- Available with four Menda pumps

	2 oz.	4 oz.	6 oz.	8 oz.
One-Touch	<b>35304</b>	<b>35305</b>	<b>35309</b>	<b>35312</b>
Pure-Touch	<b>35504</b>	<b>35505</b>	<b>35508</b>	<b>35510</b>
Take-Along	<b>35701</b>	<b>35702</b>	<b>35703</b>	<b>35704</b>
Pure-Take		<b>35803</b>	<b>35805</b>	



## Amber Glass with Stainless Steel Pump

- For applications where plastic and light sensitive fluids are used
- For solvents not compatible with plastics
- Available with One-Touch and Pure-Touch pumps
- Allows for easy viewing of contents

	4 oz.
One-Touch	<b>35315</b>
Pure-Touch	<b>35112</b>



## Tin Can with Stainless Steel Pump

- For applications where strength and durability are important
- For solvents not compatible with plastics
- One-Touch pump

	4 oz.
One-Touch	<b>35335</b>



### Did You Know ?

The best way to care for your Multi-Fluid dispenser is to wipe the dish clean between uses and periodically flush with warm water, making sure to pump all water out before returning it to the bottle

Pumps are made in America. Bottles are made and/or assembled in the USA from parts made in the USA, Japan, and the UK.