

Chipsmall Limited consists of a professional team with an average of over 10 year of expertise in the distribution of electronic components. Based in Hongkong, we have already established firm and mutual-benefit business relationships with customers from, Europe, America and south Asia, supplying obsolete and hard-to-find components to meet their specific needs.

With the principle of "Quality Parts, Customers Priority, Honest Operation, and Considerate Service", our business mainly focus on the distribution of electronic components. Line cards we deal with include Microchip, ALPS, ROHM, Xilinx, Pulse, ON, Everlight and Freescale. Main products comprise IC, Modules, Potentiometer, IC Socket, Relay, Connector. Our parts cover such applications as commercial, industrial, and automotives areas.

We are looking forward to setting up business relationship with you and hope to provide you with the best service and solution. Let us make a better world for our industry!



Contact us

Tel: +86-755-8981 8866 Fax: +86-755-8427 6832

Email & Skype: info@chipsmall.com Web: www.chipsmall.com

Address: A1208, Overseas Decoration Building, #122 Zhenhua RD., Futian, Shenzhen, China









Features:

- Clear 1 oz glass bottle with PFA stem for the toughest liquid dispensing applications – use with highly corrosive fluids, virtually all industrial solvents, and most chemicals
- Clear glass bottle allows storage of fluids not compatible with plastic and allows for easy viewing of contents
- PFA Stem has superior chemical resistivity chemically inert; resistant to acids, bases, and most common solvents.
- One handed operation is perfect for cleaning with swabs and brushes

One-Touch Pump:

- "One-Touch" one-handed operation frees operator's hands for use
- Precision machined valves for smooth consistent operation
- Recommended for one-handed dispensing of liquids, solvents, and chemicals
- Stainless-steel construction No silicone or latex suitable for ultra clean environments
- Cam-lock hinge keeps lid open and closed, reduces odors
- Dispenses approximately 0.2cc of liquid with each pump

Pump Material Stainless-Steel

Locks for Travel No Stem Material PFA

Bottle Material Glass (Clear)

Bottle Size 1 oz

Neck Size / Thread 1.25" / 38-400

Lid-Type Cam-lock hinge lid

Gasket Material LDPE



Specifications and procedures subject to change without notice. Unless otherwise noted, tolerance is ±10%.

ONE-TOUCH, 1 OZ ROUND GLASS BOTTLE WITH PFA STEM

3651 WALNUT AVE., CHINO, CA 91710

PHONE: (909) 627-2453 WEBSITE: MendaPump.com DRAWING NUMBER 35896 DATE: October 2017