

Chipsmall Limited consists of a professional team with an average of over 10 year of expertise in the distribution of electronic components. Based in Hongkong, we have already established firm and mutual-benefit business relationships with customers from, Europe, America and south Asia, supplying obsolete and hard-to-find components to meet their specific needs.

With the principle of "Quality Parts, Customers Priority, Honest Operation, and Considerate Service", our business mainly focus on the distribution of electronic components. Line cards we deal with include Microchip, ALPS, ROHM, Xilinx, Pulse, ON, Everlight and Freescale. Main products comprise IC, Modules, Potentiometer, IC Socket, Relay, Connector. Our parts cover such applications as commercial, industrial, and automotives areas.

We are looking forward to setting up business relationship with you and hope to provide you with the best service and solution. Let us make a better world for our industry!



## Contact us

Tel: +86-755-8981 8866 Fax: +86-755-8427 6832

Email & Skype: info@chipsmall.com Web: www.chipsmall.com

Address: A1208, Overseas Decoration Building, #122 Zhenhua RD., Futian, Shenzhen, China











## **Heavy Duty Dissolved Oxygen Meter**

Dual display of oxygen concentration and temperature

With RS-232 PC interface for data acquisition and datalogging applications

## **Features:**

- Large 1.4" (36mm) LCD displays both oxygen and temperature values
- Measures dissolved oxygen from 0 to 20.0mg/L and 0 to 100.0% oxygen plus temperature from 32 to 122°F (0 to 50°C)
- Automatic Temperature Compensation from 0 to 50°C via temperature probe sensor built into polarographic type oxygen probe
- Fast 0.8 second sampling time
- Recall Min/Max/Average readings and Data Hold
- Built-in RS-232 PC serial interface with optional data acquisition software and datalogger
- · Auto power off saves battery life
- Complete with 0.8" (20mm) diameter probe on 13ft (4m) cable, 5 membranes, rubber holster, 9V battery and hard case
- Optional Windows® Data Acquisition Software and serial cable enable user to display and capture readings on a PC, and set time intervals and alarms
- Optional battery operated Datalogger module stores over 8000 readings for later transfer to a PC



## **Ordering Information:**

or acrining	IIII OI III GGOIII
407510	Heavy Duty Dissolved Oxygen Kit
407510-P	Dissolved Oxygen probe with 13ft (4m) cable
780417A	Replacement Membranes (10/pack)
780418	DO Internal Fill Solution
156119	117V AC Adaptor
156221	220V AC Adaptor
407001	Data Acquisition Software and cable
380340	Rattery Önerated Datalogger Module



Specifications	Dissolved Oxygen	Oxygen	Temperature
Range:	0 to 20.0 mg/L	0 to 100.0%	32 to 122°F (0 to 50°C)
Accuracy:	±0.4 mg/L	±0.7%	±0.8°C/1.5°F
Probe Compensation			
& Adjustment:	Salt: 0 to 39%	Altitude: 0 to 3900m	Temp: 0 to 50°C
Dimensions/Weight:	7 x 2.9 x 1.3" (178 x 74 x 33mm) / 17oz (meter only) Probe: 20mm(0.8")D 125mm(4.9")L		

