



Chipsmall Limited consists of a professional team with an average of over 10 year of expertise in the distribution of electronic components. Based in Hongkong, we have already established firm and mutual-benefit business relationships with customers from,Europe,America and south Asia,supplying obsolete and hard-to-find components to meet their specific needs.

With the principle of “Quality Parts,Customers Priority,Honest Operation,and Considerate Service”,our business mainly focus on the distribution of electronic components. Line cards we deal with include Microchip,ALPS,ROHM,Xilinx,Pulse,ON,Everlight and Freescale. Main products comprise IC,Modules,Potentiometer,IC Socket,Relay,Connector.Our parts cover such applications as commercial,industrial, and automotives areas.

We are looking forward to setting up business relationship with you and hope to provide you with the best service and solution. Let us make a better world for our industry!



## Contact us

Tel: +86-755-8981 8866 Fax: +86-755-8427 6832

Email & Skype: info@chipsmall.com Web: www.chipsmall.com

Address: A1208, Overseas Decoration Building, #122 Zhenhua RD., Futian, Shenzhen, China



# COVENTRY™ Clean Room Products

Division of Chemtronics

TDS # 6200

## Poly-Wipes

### PRODUCT DESCRIPTION

**Poly-Wipes** are constructed from monofilament polyester no-run knit, providing excellent strength, good absorbency and chemical compatibility. These wipers are a perfect choice for general cleanroom and equipment maintenance, or any critical applications where lint can be detrimental. For even lower particle counts specify **6209HC** or **6259HC** with sealed edges.

- Excellent solvent and acid resistance
- Monofilament "no-run" construction does not generate loose fibers
- Excellent durability for cleaning rough, abrasive, or irregular surfaces
- Low ionic, nonvolatile residue and particle contamination
- Good absorbency
- Available in heavy or light weight styles
- Available stacked or bulk packed
- Processed and packaged in a Class 10 cleanroom.

### TYPICAL APPLICATIONS

Poly-Wipes can be used to clean:

- Semiconductor Wafer Fabs
- Aerospace Production Areas
- Disk Drives Production Areas
- Pharmaceutical / Biotechnical Production Areas
- General Cleanroom Cleaning
- Clean and polish critical surfaces both metal and non-metal

### COMPATIBILITY

**Poly-Wipes** are compatible with most common solvents such as isopropyl alcohol, methanol and ketones such as acetone or methyl ethyl ketone. These wipes are generally compatible with dilute or weak bases, as well as with most dilute or weak acids.

### AVAILABILITY

#### 6200 Series Poly-Wipes (Standard Weight)

**6209** 9" x 9" (22.9cm x 22.9cm) Polyester wipe, 125g/m<sup>2</sup>, 150/Bag

**6209HC** 9" x 9" (22.9cm x 22.9cm) Sealed Edge Polyester wipe, 140g/m<sup>2</sup>, 150/Bag

#### 6250 Series Poly-Wipes (Heavy Weight)

**6259** 9" x 9" (22.9cm x 22.9cm) Polyester wipe, 143g/m<sup>2</sup>, 150/Bag

**6259HC** 9" x 9" (22.9cm x 22.9cm) Sealed Edge Polyester wipe, 140g/m<sup>2</sup>, 150/Bag

COVENTRY™ Clean Room Products

Division of Chemtronics

8125 Cobb Center Drive

Kennesaw, GA 30152 USA

1-770-424-4888

REV. A (08/13)

**TECHNICAL HOT LINE 1-800-TECH-401**

# Poly-Wipes Test Data

Wipe Material	Polyester Knit Fabric (70 denier)			
Wipe	6200 Series	6250B Series	6250 Series	6250LE Series
Availability	9"x9" (6209)	6"x6"(6256B)	4" x 4" (6254) 9" x 9" (6259)	9" x 9"(6259LE)
Basis Weight	125 g/m <sup>2</sup> (+/- 5 g/m <sup>2</sup> )	143 g/m <sup>2</sup> (+/- 5 g/m <sup>2</sup> )	143 g/m <sup>2</sup> (+/- 5 g/m <sup>2</sup> )	140 g/m <sup>2</sup> (+/- 5 g/m <sup>2</sup> )
Particle Counts (LPC) >/= 0.5 microns	11 million/m <sup>2</sup>	17 million/m <sup>2</sup>	12 million/m <sup>2</sup>	9.2 million/m <sup>2</sup>
NVR in DI water	None Detected	None Detected	0.053 g/g	None Detected
NVR in IPA	None Detected	None Detected	0.22 g/g	None Detected
FTIR : silicone, amide, phthalates	None Detected	None Detected	None Detected	None Detected
Chloride Ions	None Detected	0.001 g/g	0.007 g/g	None Detected
Flouride Ions			None Detected	None Detected
Nitrite Ions			None Detected	None Detected
Nitrate Ions			None Detected	None Detected
Phosphate Ions			None Detected	None Detected
Sulphate Ions	None Detected	0.004 g/g	0.001 g/g	0.001
Sodium Ions			0.001 g/g	0.001
Calcium Ions			0.0015 g/g	0.0012
Zinc Ions			None Detected	None Detected
Ammonium		0.021 g/g	None Detected	None Detected
Absorbency	365 ml/m <sup>2</sup>	412 ml/m <sup>2</sup>	412 ml/m <sup>2</sup>	410 ml/m <sup>2</sup>

The wipe tests were done using the recommended practices of the Institute of Environmental Science, Swabs and Wipes Working Group.

## TECHNICAL AND APPLICATION ASSISTANCE

Coventry™ Clean Room Products provides A technical hotline to answer your technical And application related questions.

The toll free number is: **1-800-TECH-401**

**DISTRIBUTED BY:**

Chemtronics® is a registered trademark of Chemtronics. All rights reserved. Coventry™ is a trademark of Chemtronics. All rights reserved.

**TECHNICAL HOT LINE 1-800-TECH-401**