



Chipsmall Limited consists of a professional team with an average of over 10 year of expertise in the distribution of electronic components. Based in Hongkong, we have already established firm and mutual-benefit business relationships with customers from,Europe,America and south Asia,supplying obsolete and hard-to-find components to meet their specific needs.

With the principle of “Quality Parts,Customers Priority,Honest Operation,and Considerate Service”,our business mainly focus on the distribution of electronic components. Line cards we deal with include Microchip,ALPS,ROHM,Xilinx,Pulse,ON,Everlight and Freescale. Main products comprise IC,Modules,Potentiometer,IC Socket,Relay,Connector.Our parts cover such applications as commercial,industrial, and automotives areas.

We are looking forward to setting up business relationship with you and hope to provide you with the best service and solution. Let us make a better world for our industry!



## Contact us

Tel: +86-755-8981 8866 Fax: +86-755-8427 6832

Email & Skype: info@chipsmall.com Web: www.chipsmall.com

Address: A1208, Overseas Decoration Building, #122 Zhenhua RD., Futian, Shenzhen, China





**SPI**

- Medical grade stainless steel interior expansion band will not cause allergic skin reactions for most people
- Non-flaking or scratching laminated insulator on all external surfaces protects wearers from electrical hazards
- Superior contact with skin with more reliable path-to-ground
- Designed to be used with Dual-Wire Coil Cords and Dual-Wire Continuous Monitors
- Available in large, medium or small sizes
- 7mm sockets

"Typical test programs recommend that wrist straps that are used daily should be tested daily. However, if the products that are being produced are of such value that knowledge of a continuous, reliable ground is needed, and then continuous monitoring should be considered or even required." (ESD Handbook TR 20.20 section 5.3.2.4.4)

"All personnel shall be bonded or electrically connected to the grounding / equipotential bonding system when handling ESDS [ESD sensitive] items." (ANSI/ESDS20.20-2007 section 8.1)

"When personnel are seated at ESD protective workstations, they shall be connected to the grounding / equipotential bonding system via a wrist strap system." (ANSI/ESDS20.20-2007 section 8.2)

ITEM	DESCRIPTION	CIRCUMFERENCE	
		MIN	MAX
63208	Dual-wire Metal Wristband only, 7mm sockets, M	6" (152.4mm)	11" (279.4mm)
63210	Dual-wire Metal Wristband only, 7mm sockets, S	5.5" (139.7mm)	9" (228.6mm)
63110	Dual-wire Metal Wrist Strap, with 6' Coil Cord, 7 mm sockets, L	7" (177.8mm)	12" (304.8mm)
63112	Dual-wire Metal Wrist Strap, with 6' Coil Cord, 7 mm sockets, M	6" (152.4mm)	11" (279.4mm)
63114	Dual-wire Metal Wrist Strap, with 6' Coil Cord, 7 mm sockets, S	5.5" (139.7mm)	9" (228.6mm)
63131	Dual-wire Metal Wrist Strap, with 12' Coil Cord, 7 mm sockets, M	6" (152.4mm)	11" (279.4mm)
63132	Dual-wire Metal Wrist Strap, with 12' Coil Cord, 7 mm sockets, S	5.5" (139.7mm)	9" (228.6mm)

See drawing 63488 for coil cord details.



### SEMTRONICS WRISTBAND, DUAL, METAL, 7MM SOCKET

**ESD SYSTEMS.com**

ESD SYSTEMS.COM  
432 NORTHBORO ROAD CENTRAL  
MARLBORO, MA 01752 USA  
TEL. (508) 485-7390 FAX (508) 480-0257



Visit our online  
library of Tech Drawings:  
ESDSystems.com

**DRAWING  
63208**

**DATE:**  
October  
2008