

Chipsmall Limited consists of a professional team with an average of over 10 year of expertise in the distribution of electronic components. Based in Hongkong, we have already established firm and mutual-benefit business relationships with customers from, Europe, America and south Asia, supplying obsolete and hard-to-find components to meet their specific needs.

With the principle of "Quality Parts, Customers Priority, Honest Operation, and Considerate Service", our business mainly focus on the distribution of electronic components. Line cards we deal with include Microchip, ALPS, ROHM, Xilinx, Pulse, ON, Everlight and Freescale. Main products comprise IC, Modules, Potentiometer, IC Socket, Relay, Connector. Our parts cover such applications as commercial, industrial, and automotives areas.

We are looking forward to setting up business relationship with you and hope to provide you with the best service and solution. Let us make a better world for our industry!



Contact us

Tel: +86-755-8981 8866 Fax: +86-755-8427 6832

Email & Skype: info@chipsmall.com Web: www.chipsmall.com

Address: A1208, Overseas Decoration Building, #122 Zhenhua RD., Futian, Shenzhen, China







Tuffman Pressure Meter TPI 635 / 645 / 655



Visit TPI, The Value Leader at: www.tpi-thevalueleader.com

Table of Contents

Page 3 Introduction & Product Description

Page 4 Safety Considerations

Page 5 Technical Data & International Symbols

Page 6 Features & Benefits

Page 7 Pressure Conversion Table

Page 8 Step by Step Procedures

Page 9 Accessories & Specifications

Page 10 Maintenance

Page 11 Trouble Shooting Guide EC declaration of conformity

Page 12 Warranty Statement

Introduction

Congratulations!

Thank you for purchasing TPI brand products. This meter is easy to use and is built to last. It is backed by a 3 year limited warranty. Please remember to return your product warranty registration card.

Product Description

The TPI 600 Tuffman series is a hand held range Of pressure meters and can be summarized as follows.

TPI 635 5 PSI pressure range

TPI 645 30 PSI pressure range

TPI655 100 PSI pressure range

All of these models are dual input differential pressure meters with 7 selectable scales to choose from: mbar, kPa, PSI, inHg. mmHg,inH20, and mH20.

Safety Considerations

WARNING: Please follow the manufacture's test procedure whenever possible. Make sure the pressure to be measured is not outside the range of the TPI 635/645/655 meter.

General Guidelines

ALWAYS

- Test the pressure meter before use to ensure it is operating properly
- Ensure that the connecting hose you are using is free from kinks or splits
- Double check all connections before testing

NEVER

- Connect the instrument to an unknown pressure source if the source is twice the working pressure of the instrument the sensor will be damaged and may cause injury to the user
- Tamper with the instrument or attempt to modify it in any way.
 Otherwise accident and injury may occur and the warranty be comes void.

Technical Data

Controls TPI 635/645/655

ON Switches instrument "ON" for use
OFF Switches instrument "OFF" after use

ZERO Automatically "zero's" the instrument

Smoothing function to stabilize rapidly changing readings

MAX/MIN Enables user to recall & display both the maximum and

minimum pressure recorded since the function was selected. Press button once to activate, twice to read minimum and

three times to read the maximum. To cancel the function press

and the hold the "MAXIMIN" button

HOLD Maintains the reading on the LCD display

UNITS Selects 7 units of measure kPa, PSI, inHg, mmHg, inH20,

mH 20, mbar

Features & Benefils

Auto ranging- Provides high resolution & accuracy at low pressures

where it is needed

Auto Power Off- Powers off after 30 minutes to conserve battery life.

Trim Mode- Smoothing function to stabilize erratic readings.

It displays the average value of 4 values previously

measured.

Zero function- Provides immediate push-button zeroing for Speed

and accuracy.

Record Max/Min- Enables long term testing of pressure systems for leaks

Hold- Enables the user to freeze the display reading, when

working in cramped working conditions, when the

display is not visible.

Units- Change the display value in anyone of the following

engineering units. kPa, PSI, inHg, mmHg, inH20,

mH20 and mbar.

Pressure Conversion Table

	Atmos	mbar	inHg	inH20	PSI	mmHg	mH20	kPa
Atmos	1	9.86923 x 10⁴	3.34207 X 10 ⁻²	2.45832 X 10 ⁻³	6.8046 X 10 ⁻²	1.31579 X 10 ⁻³	9.67841 X 10 ⁻³	9.86923 X 10 ⁻³
mbar	1013.25	1	33.8638	2.49089	68.9476	1.33322	98.0665	10
inHg	29.9213	2.95301 x 10 ⁻²	1	7.35561 X 10 ⁻²	2.036	3.937 X 10 ⁻²	2.89591	0.295301
in H20	406.8	0.401463	13.5951	1	27.68	0.534	39.3701	4.01463
PSI	14.6959	1.45038 x 10 ⁻²	0.491153	3.61273 X 10 ⁻²	1	1.934 X 10 ⁻²	1.42233	0.145038
mmHg	760	0.750064	25.4	1.86833	51.715	1	73.5561	7.50064
mH20	10.3323	1.01972 x 10 ⁻²	0.345315	2.54 X 10 ⁻²	0.70307	1.35951 X10 ⁻²	1	0.101972
kPa	101.325	0.1	3.38638	0.249089	6.89476	0.133322	9.80665	1

Step by Step Procedures

- Press the "ON" key and the LCD display will be activated if it does not read 0.00 proceed as follows
- Press the "zero" key and the display should read zero. if not repeat until it does
- Connect pressure meter to installation or equipment to be tested using appropriate hose connection in accordance with the manufactures instructions
- The pressure reading will appear on the display. To activate the backlight in poor light conditions press the "ON' key at any time
- If the reading is erratic or changing activate the smoothing unction by pressing the" =" key
- To freeze a reading in awkward or cramped working spaces press the "Hold" key
- To record maximum & minimum pressures when establishing pressure decay or carrying out gas line soundness testing press the "MAXIMIN" key
- To convert the displayed pressure reading to another engineering unit depress the "Unit" key anytime and scroll through to the desired units of pressure.

Accessories & Specifications

Standard Accessories	Part No.
9V ALKALINE battery	A009A
Replacement tubing t/4" 00 x 28"(L)	A601
Optional Accessories	Part No.
Replacement tubing 1/4' 00 x 28" T Fitting	A605
Large Zippered Case	A904
9V lithium battery	U9VL

Features	Mode	el 635	645	655			
Range		5 PSI	30 PSI	100 PSI			
Accuracy		±0.2'% of full scale +3 digits					
Over Press	ure -	14.5 psi (1000 mbar)	58.0 psi (4000 mbar)	145 psi (10 bar)			
Power Sup	ply	9V					
Relative Humidity		0% to 80% (a· to + 40°C)					
Operating Temp.		32° to 104°F (D' to +40°C)					
Storage Temp.		14° to 122°F (-10"10 + 50'C)					
Auto Power Off		After 30 minutes					
Trim Mode		Yes					
Zero Adjust			Yes Push Button				
Data Hold			Yes				
Record			Yes Max/Min				

Maintenance Battery Replacement

The 635/645/655 will display a iBATi symb 01 when the internal 9V battery needs replacement. Replace battery as follows:

- 1. Ensure instrument is switched off
- 2. Loosen the cross head screw on the battery compartment cover
- 3. Remove battery compartment cover
- 4. Remove old battery
- 5. Replace with new battery 9V NEDA 1604 or equivalent
- 6. Reassemble the instrument in reverse order from above
- 7. RE-fit the cross head screw being sure not to over tighten

Cleaning

Use a mild detergent and a slightly damp cloth to clean the surfaces of the instrument.

Trouble Shooting Guide

Problem Pro bable Cause

Unit does not zero Zero button has not been operated

Unit still does not zero If reading is greater than 0.05 and constantly fluctuation return to local service centre

iBati appears on the display Replace battery immediately 9V NEDA

15050cequivalent

EC Declaration 01 Conformity

This is to certify that model 634/645/655 conform to the protection requirements of the council directive 89/336/EEC, in the approximation of laws of the member states relating to Electromagnetic compatibility by application of the following standards

EN50081-1 1992 Emissions Standard EN50082-1 1992 Immunity Standard

To ensure conformity with these standards, this instrument must be operated in accordance with the instructions and specifications given in this manual.

Warranty Statement 3 Year Limited Warranty

This TPI product is warranted to the purchaser against defect in materials and workmanship for 3 years from the date of purchase.

Covered by TPI: Repair parts and labour; or replacement of the product at the option of TPI. Normal transportation charges to the purchaser are also covered.

Not covered by TPI: Damage to the product which are the result of abuse, improper use or maintenance are not covered. Any other expense, consequential damages, incidental expenses including damages to property is not covered. Transportation expense to the company are not covered.

To obtain warranty performance: include with the product your name, address, phone number, written description of the problem and proof of purchase date. Carefully package and return to the address printed below.

Test Products International, Ltd. 342 Bronte SI. South Unit #9 Miltoll, Ontario L9T 5B7 Canada

905-693-8558 Fax: 905 -693-0888

e-mail: inlo@lpicanada.com

Test Products International, Inc Headquarters 9615 SW Allen Blvd. Beaverton, OR 97005 USA

503-520-91971 Fax: 503-520-1225 e-mail: inlo@tpi-lhevalueleader.com