



Chipsmall Limited consists of a professional team with an average of over 10 year of expertise in the distribution of electronic components. Based in Hongkong, we have already established firm and mutual-benefit business relationships with customers from,Europe,America and south Asia,supplying obsolete and hard-to-find components to meet their specific needs.

With the principle of “Quality Parts,Customers Priority,Honest Operation,and Considerate Service”,our business mainly focus on the distribution of electronic components. Line cards we deal with include Microchip,ALPS,ROHM,Xilinx,Pulse,ON,Everlight and Freescale. Main products comprise IC,Modules,Potentiometer,IC Socket,Relay,Connector.Our parts cover such applications as commercial,industrial, and automotives areas.

We are looking forward to setting up business relationship with you and hope to provide you with the best service and solution. Let us make a better world for our industry!



Contact us

Tel: +86-755-8981 8866 Fax: +86-755-8427 6832

Email & Skype: info@chipsmall.com Web: www.chipsmall.com

Address: A1208, Overseas Decoration Building, #122 Zhenhua RD., Futian, Shenzhen, China



Gloves - eliminates the need for wristbands. To verify path-to-ground, test resistance path using wrist strap tester. With glove on one hand touch test button with bare (ungloved) finger.
 Two piece design for comfort and ambidextrous use, non-allergenic.
 Can be grounded to smock or wrist strap ground cord.

- A. 0.060" (4mm) stud to fit 4 ground cords with 1/8" (4mm) spring loaded medical snap.*
- B. Base fabric is 98.5% textured polyester. Conductive fiber filament (RTT: 10^7 Ohms) made of carbon suffused nylon 6 monofilament spaced every 0.25".


Material will not slough and is safe for use in cleanrooms down to class 100.

Can be washed multiple times in a mild detergent.

- C. Conductive, color coded cuff (see chart below) interconnects with the conductive fiber and snap providing a true and rapid ground path.

D. Glove length.

E. Finger width.




	WOMEN'S				MEN'S			
SIZE	PART #	CUFF COLOR	D	E	PART #	CUFF COLOR	D	E
SMALL	68102	PINK	6"	2 1/2"	68105	BEIGE	7"	2 3/4"
MEDIUM	68101	RED	6"	2 3/4"	68104	BLUE	7"	3 1/8"
LARGE	68100	ORANGE	6"	3 1/8"	68103	BROWN	7"	3 3/8"
X-LARGE	-	-	-	-	68106	GREY	7"	3 5/8"

*Glove should be grounded, and tested to verify dissipation of static charges. Use Desco 09480 or equivalent to ground.

Glove Laundering

For proper operation, the ESD Gloves must be laundered periodically. Woolite works well. Liquid detergents are better than dry in that there is less caking and frictional wear. Launder glove in cool or warm water, tumble dry with low heat or hang dry. Machine washing works well if using a standard house machine on gentle cycle. It is not recommended to launder these gloves in heavy industrial laundry machines as it will lead to premature wear. Gloves should be tumbled dry using low heat. DO NOT BLEACH. After laundering, verify RTT 10^7 ohms.



STATIC DISSIPATIVE GLOVES

DESCO WEST: 3651 WALNUT AVE., CHINO, CA 91710 WEB SITE: www.desco.com
 PHONE (909) 627-8178 FAX (909) 627-7449

DESCO EAST: ONE COLGATE WAY, CANTON, MA 02021-1407
 PHONE (781) 821-8370 FAX (781) 575-0172

DRAWING NUMBER
68100

DATE:
January
2009

