



Chipsmall Limited consists of a professional team with an average of over 10 year of expertise in the distribution of electronic components. Based in Hongkong, we have already established firm and mutual-benefit business relationships with customers from,Europe,America and south Asia,supplying obsolete and hard-to-find components to meet their specific needs.

With the principle of “Quality Parts,Customers Priority,Honest Operation,and Considerate Service”,our business mainly focus on the distribution of electronic components. Line cards we deal with include Microchip,ALPS,ROHM,Xilinx,Pulse,ON,Everlight and Freescale. Main products comprise IC,Modules,Potentiometer,IC Socket,Relay,Connector.Our parts cover such applications as commercial,industrial, and automotives areas.

We are looking forward to setting up business relationship with you and hope to provide you with the best service and solution. Let us make a better world for our industry!



## Contact us

Tel: +86-755-8981 8866 Fax: +86-755-8427 6832

Email & Skype: info@chipsmall.com Web: www.chipsmall.com

Address: A1208, Overseas Decoration Building, #122 Zhenhua RD., Futian, Shenzhen, China



**Data Sheet**



**PH electrode**  
**Model 760PH**

- Plug in the 760 to be a PH electrode Meter.
- Range: 0 to 14 PH
- Measuring Temp.: 0°C to 100°C



**ATC PROBE**  
**Model 760ATC**

- Plug in the 760 to be a ATC (Automatic Temp. Compensation) probe to gain the Max. possible accuracy.
- Temperature range: 0 to 65 °C, 32 to 149 °F.



**DISSOLVED OXYGEN PROBE**  
**Model 760DOP**

- Plug in the 760 to be a professional Dissolved Oxygen Meter.
- Range: 0 - 20.0 mg/L, 0.1 mg/L.
- With automatic temperature: 0 - 50.0 °C, 0.1 °C/0.1 °F.
- Diaphragms & electrolyte included.



**CONDUCTIVITY PROBE**

- Model 760CP**
- plug in the 760 to be a professional Conductivity Meter,
  - Conductivity : 2/20 mS, 2 ranges
  - Temperature : 0 to 60.0 °C/0.1 °F.
  - ATC & variable temp. compensation factor adjustment (0 to 5.0% per °C).

**INTELLIGENT PH METER**

**Model 760**

- PH Meter with mV and "plug and play" function.
- pH (0.00 to 14.00 pH), mV (± 1999 mV).
- manual temp. compensation adj. or ATC via the optional temp. probe (760 ATC).
- Be plugged with "plug and play" probes: 760CP, 760DOP, 760ATC to be a professional Conductivity Meter, ATC Meter, Dissolved Oxygen Meter.
- RS-232, Hold, Memory record, °C/°F, 0.1 degree.
- Patent obtained.



**SOFTWARE W/RS-232 CABLE**

**Model AK 760**

- For windows 95 & 98
- Data logging system, data recorder



**PROTECTIVE CARRYING CASE**

**Model LC 760**

- Dimensions: (HxWxD) 2.75" x 15" x 10"

**B&K Precision Corporation**

22820 Savi Ranch Parkway, Yorba Linda, CA 92887  
Tel: 714-921-9095, Fax: 714-921-6422  
www.bkprecision.com

Specifications subject to change without notice