

Chipsmall Limited consists of a professional team with an average of over 10 year of expertise in the distribution of electronic components. Based in Hongkong, we have already established firm and mutual-benefit business relationships with customers from, Europe, America and south Asia, supplying obsolete and hard-to-find components to meet their specific needs.

With the principle of "Quality Parts, Customers Priority, Honest Operation, and Considerate Service", our business mainly focus on the distribution of electronic components. Line cards we deal with include Microchip, ALPS, ROHM, Xilinx, Pulse, ON, Everlight and Freescale. Main products comprise IC, Modules, Potentiometer, IC Socket, Relay, Connector. Our parts cover such applications as commercial, industrial, and automotives areas.

We are looking forward to setting up business relationship with you and hope to provide you with the best service and solution. Let us make a better world for our industry!



Contact us

Tel: +86-755-8981 8866 Fax: +86-755-8427 6832

Email & Skype: info@chipsmall.com Web: www.chipsmall.com

Address: A1208, Overseas Decoration Building, #122 Zhenhua RD., Futian, Shenzhen, China









American Hakko Products, Inc.

PRODUCT BULLETIN

Bulletin No: PB336

Issue Date: 5-6-2013

Available: 5-10-2013

Product Description:

Odor Filter for the Hakko FA-430

Part No: 999-245

Specification:

Unit	270 x 220 x 125mm
	(10.6 x 8.6 x 5 in.)
Shipping	292 x 229 x 165 mm
	(11.5 x 9 x 6.5 in.)
Unit	1679 g (3.7 lb.)
Shipping	1951 g (4.3 lb.)
ency	>98% of particulate to 0.3 μ m
	Activated Carbon
	1.239 m ² (13.34 ft ²)
bon	600g
ly Level	1100 mg/g minimum
ide No.	60%
apacity	Approx. 360g ¹
	Shipping Unit



Comment:

The Hakko 999-245 Carbon Odor Filter is designed as an optional filter that can be used in the Hakko FA-430 Fume Extraction System when the primary use of the system is to remove odors created by various processes. The pleated media contains highly activated carbon and provides a greater gas adsorption area compared to the activated carbon portion of the standard main filter that comes with the Hakko FA-430 Fume Extraction System.

NOTE: This filter will also trap particulates therefore the use of the Hakko A1585 Pre-Filter is required to ensure maximum filter life.

For more information, visit us online at www.HakkoUSA.com or call us at 1-800-88-HAKKO (42556).

^{1 –} Adsorption Capacity based on ASTM D3467 for Carbon Tetrachloride Activity of Activated Carbon