

Chipsmall Limited consists of a professional team with an average of over 10 year of expertise in the distribution of electronic components. Based in Hongkong, we have already established firm and mutual-benefit business relationships with customers from, Europe, America and south Asia, supplying obsolete and hard-to-find components to meet their specific needs.

With the principle of "Quality Parts, Customers Priority, Honest Operation, and Considerate Service", our business mainly focus on the distribution of electronic components. Line cards we deal with include Microchip, ALPS, ROHM, Xilinx, Pulse, ON, Everlight and Freescale. Main products comprise IC, Modules, Potentiometer, IC Socket, Relay, Connector. Our parts cover such applications as commercial, industrial, and automotives areas.

We are looking forward to setting up business relationship with you and hope to provide you with the best service and solution. Let us make a better world for our industry!



# Contact us

Tel: +86-755-8981 8866 Fax: +86-755-8427 6832

Email & Skype: info@chipsmall.com Web: www.chipsmall.com

Address: A1208, Overseas Decoration Building, #122 Zhenhua RD., Futian, Shenzhen, China







# ADNS-5100/ADNS-5100-001

Solid-State Optical Mouse Lens



# **Data Sheet**

#### **Description**

The ADNS-5100 and ADNS-5100-001 Solid-State Optical Mouse Lenses are designed for use with the ADNS-5XXX series of Avago Technologies Optical Mouse Sensors. The optical system is completed with the illumination subsystem provided by the ADNS-5200 LED Assembly Clip and the HLMP-ED80-XX000 LED. Together with the LED, the ADNS-5100 and ADNS-5100-001 provides the directed illumination and optical imaging necessary for proper operation of the Optical Mouse Sensor. The lenses are precision molded optical components and should be handled with care to avoid scratching of the optical surfaces.

#### **Ordering Information**


Specify Part Number as follows:

Flange	Part Number	Material		
Round	ADNS-5100	Polycarbonate or Polystyrene HH30		
Trim	ADNS-5100-001	Polycarbonate or Polystyrene HH30		

### **Outline Drawings Including Markings and Logos**

LENS SURFACE 2

#### **ADNS-5100**



LENS SURFACE 6

Lens ID

Figure 1. ADNS-5100 Solid State Optical Mouse Round Lens outline drawing and detail

LOGO

# **Outline Drawings Including Markings and Logos**

# ADNS-5100-001




Figure 2. ADNS-5100-001 Solid State Optical Mouse Trim Lens outline drawing and detail

# **Mechanical Assemble Requirements**

All specifications reference Figure 3, Optical System Assembly Diagram

	Symbol	Min.	Typical	Max.	Units	Conditions
Distance from Object Surface to Lens Reference Plane	А	2.3	2.4	2.5	mm	
Distance from Mouse Sensor Lid contact with lens Surface to Object Surface	В		7.38		mm	Sensor lid must be in contact with lens housing surface




Figure 3. Optical System Assembly Diagram

# **Lens Design Optical Performance Specifications**

All specifications are based on the Mechanical Assembly Requirements.

	Symbol	Min.	Typical	Max.	Units	Conditions
Numerical Aperture	NA	0.1	0.13	0.16		
Magnification			1.25			Image at nominal location
Design Wavelength			639		nm	
Object to Image Distance			8.83		mm	
Lens Material*Index of Refraction	N	1.580	1.582	1.5840		λ = 639nm
Depth of Field	DOF		±0.5		mm	
Die Coverage Radius			0.6		mm	

<sup>\*</sup>Lens material is polycarbonate or polystyrene HH30, therefore, cyanoacrylate based adhesives should not be used as they will cause lens material deformation.

# Mounting Instructions for the ADNS-5100 Lens to the Base Plate

An IGES format drawing file with design specifications for mouse base plate features is available.

Note:- Stand-off of the base plate shall not be larger than 5mm as lens surface 7 size is 5.60mm."




Figure 4. Illustration of base plate mounting features

These features are useful in maintaining proper positioning and alignment of the ADNS-5100 when used with the Avago Technologies Optical Mouse Sensor. This file can be obtained by contacting your local Avago Technologies sales representative.

For product information and a complete list of distributors, please go to our web site:

www.avagotech.com

