mail

Chipsmall Limited consists of a professional team with an average of over 10 year of expertise in the distribution of electronic components. Based in Hongkong, we have already established firm and mutual-benefit business relationships with customers from, Europe, America and south Asia, supplying obsolete and hard-to-find components to meet their specific needs.

With the principle of "Quality Parts, Customers Priority, Honest Operation, and Considerate Service", our business mainly focus on the distribution of electronic components. Line cards we deal with include Microchip, ALPS, ROHM, Xilinx, Pulse, ON, Everlight and Freescale. Main products comprise IC, Modules, Potentiometer, IC Socket, Relay, Connector. Our parts cover such applications as commercial, industrial, and automotives areas.

We are looking forward to setting up business relationship with you and hope to provide you with the best service and solution. Let us make a better world for our industry!



Contact us

Tel: +86-755-8981 8866 Fax: +86-755-8427 6832 Email & Skype: info@chipsmall.com Web: www.chipsmall.com Address: A1208, Overseas Decoration Building, #122 Zhenhua RD., Futian, Shenzhen, China





Model No: BMR85DD NA8Y

Product Line: Tymphany

Product Description

This 80hm 4.5inch full range transducer is a member of the new BMR family. This driver features a powerful neodymium magnet , nestled within an innovative suspension system. The motor contains a copper cap to lower inductance and distortion. The flat cone is honeycomb paper material, with rubber surround, with plastic basket. Is designed to be a high performance full range driver. This family driver is used for shallow applications such as television soundbars and compact music system.

Driver Specification Sheet


Rev: 4 Last Update: 2017-04-21 12:42:13



Specifications

DC Resistance	Revc	Ohms	7.57	5.0%	Energy Bandwidth Product	EBP	(1/Qes)*fs	
Minimum Impedance	Zmin	Ohms	8.81	7.5%	Moving Mass	Mms	g	8.3
Voice Coil Inductance	Le	mH	0.04		Suspension Compliance	Cms	um/N	404.3
Resonant Frequency	Fs	Hz	86.75	15%	Effective Cone diameter	D	cm	9.3
Mechanical Q Factor	Qms		3.47		Effective Piston Area	Sd	cm^2	67.9
Electrical Q Factor	Qes	0.99			Effective Volume	Vas	L	2.62
Total Q Factor	Qts		0.77		Motor Force Factor	BL	Tm	5.9
Ratio Fs/Qts	F	Fs/Qts	112.8		Motor Efficiency Factor	ß	(T*M^2)/Ohms	4.6
Half Space Sensitivity @2.83V	db@2.83V/1M	dB	85.02	+/- 1.0db	Voice coil former Material	VCfm		ASV
Half Space Sensitivity @1W/1M	db@1W/1M	dB	85.4	+/- 1.0db	Voice coil inner diameter	VCd	mm	32
Gap Height	Gh	mm	4		Rated Noise Power	Р	W	20
Maximum Linear Excursion	Xmax	mm	0.7		Test Spectrum Bandwidth	20Hz-12KHz		
Ferrofluid Type	FF				Driver Size	Inch	4 in	
Driver Mass	Kg	0.22						

Frequency and Impedance Response



Tymphany HK LTD Address : Room 1307-8 Dominion Centre, 43-59 Queens Rd East, Wanchai, Hong Kong E-mail: sales@tymphany.com