



Chipsmall Limited consists of a professional team with an average of over 10 year of expertise in the distribution of electronic components. Based in Hongkong, we have already established firm and mutual-benefit business relationships with customers from,Europe,America and south Asia,supplying obsolete and hard-to-find components to meet their specific needs.

With the principle of “Quality Parts,Customers Priority,Honest Operation,and Considerate Service”,our business mainly focus on the distribution of electronic components. Line cards we deal with include Microchip,ALPS,ROHM,Xilinx,Pulse,ON,Everlight and Freescale. Main products comprise IC,Modules,Potentiometer,IC Socket,Relay,Connector.Our parts cover such applications as commercial,industrial, and automotives areas.

We are looking forward to setting up business relationship with you and hope to provide you with the best service and solution. Let us make a better world for our industry!



## Contact us

Tel: +86-755-8981 8866 Fax: +86-755-8427 6832

Email & Skype: info@chipsmall.com Web: www.chipsmall.com

Address: A1208, Overseas Decoration Building, #122 Zhenhua RD., Futian, Shenzhen, China







Smart Technology. Delivered.™

# Thermoelectric Assemblies





## About Laird

Laird is a global technology company focused on providing systems, components and solutions that protect electronics from electromagnetic interference and heat, and that enable connectivity in mission-critical wireless applications and antenna systems.


We are a global leader in the field of radio frequency (RF) engineering and in the design, development and supply of innovative technology that allows people, organisations and applications to connect efficiently.

Our aim is to be a trusted partner to our customers by delivering problem-solving solutions through Innovation, Reliable Fulfilment, and Speed.

Laird partners with its customers to design custom thermal solutions for applications in many industries including:

- Medical Diagnostics
- Medical Imaging
- Battery Cooling
- Industrial Laser Systems
- Optoelectronics
- Analytical Instrumentation
- Semiconductor Fabrication
- Aerospace Defense
- Food & Beverage
- Automotive

As an industry leader in high-performance Engineered Thermal Systems that demand high system uptime, Laird provides the knowledge, innovation, and resources to ensure exceptional thermal performance and customer satisfaction for applications in the medical, analytical, telecom, industrial, and consumer markets.



## Introduction

Thermoelectric Assemblies (TEAs) are compact units that control the temperature of a wide variety of applications, such as laser diode packages in active optics, lasers in medical and industrial instrumentation, electronic enclosures, sample storage chambers in medical diagnostics and analytical instruments and batteries in various automotive and telecom applications. TEAs serve a cooling capacity spectrum from approximately 10 to 400 Watts, and can cool by removing heat from control sources through convection, conduction, or liquid means.

## Advantages

TEAs offer several advantages over other cooling technologies. For example, conventional fan trays do not cool to below ambient and require an air exchange with the outside environment. On the other hand, TEAs can cool to well below ambient and protect electronics inside enclosures from outside contaminants, and also limit moisture exposure from the outside environment. TEAs also offer precise temperature control and accuracies to within 0.01°C are achievable under steady-state conditions.

- TEAs have several advantages over conventional compressor-based systems:
- Compact size and lower weight than conventional compressor-based systems
- Mountable in any orientation and have lower noise and vibration
- Environmentally friendly, as TEAs do not use CFCs and are RoHS compliant
- Low to no field maintenance requirement, which lowers the total cost of ownership.

Engineers must now consider thermal management early in the product design process. Simple thermal management solutions, such as adding a fan or heat sink, are no longer typically viable to meet required performance and reliability specifications.

A standard TEA allows the designer to start with a basic set of building blocks that mate fans and TEMs to heat exchangers. Laird has conducted two decades worth of design and validation testing on various combinations of thermal components to optimize cooling power and efficiency at various heat loads. This results in engineers saving time with redesign and validation testing a TEA that has already been perfected by Laird.

Below is a summary of inherent benefits of initiating a thermal design with a standard TEA versus a custom solution:

1. Reduce product development time by initiated product at TEA level vs TEM level.
2. Reduce costs by utilizing components that are already established in the supply chain.
3. Long term history of products in field provide reliable field data of robustness of products in operation.
4. Product enhancements are captured through market evolution.

## TEA Portfolio

Laird offers the widest selection of TEAs on the market. Products are designed and manufactured to strict process control standards and pass/fail criteria, assuring that our customers receive the best possible TEAs. Our standard product portfolio includes an extensive array of thermal management solutions that cover a wide range of cooling capacities with compact form factors and high coefficient of performance. Standard operating voltages are 12 and 24 VDC, and on some models 48 VDC. The standard product offering includes heat transfer mechanisms designed to absorb and dissipate heat by convection, conduction, or through liquid heat exchangers. All products are manufactured in an ISO 9001:2008 certified facility and are designed to meet the cooling needs of many thermal management applications in the medical, analytical, industrial and telecom markets.

There are five distinct TEA product families that were designed for a specific cooling capacity range, temperature differential range or tight space constraint. The diagram to the right is a perceptual map of a cooling spectrum that can be used to guide designers to a particular product family that will have the desired attributes that the application requires.

## Thermoelectric Applications

Thermoelectric Assemblies are used in a wide range of applications to stabilize the temperature of sensitive electronic components or to cool devices and compartments below ambient.

### Telecommunications


Cooling below ambient is necessary to extend life of batteries in wireless base stations. Temperature stabilization is required to maintain peak performance of laser diodes.

- Telecom Enclosures
- Battery Backup Systems
- High Powered Laser Diodes

### Medical

Temperature stabilization is required to obtain a high image resolution. Cooling reagent chambers below ambient is critical to extend life of reagents and keep replacement costs down. Rapid thermal cycling is crucial to speed up DNA amplification.

- Medical Imaging
- Clinical Diagnostics
- Medical Lasers
- Analytical Instrumentation
- PCR



## Industrial & Instrumentation

Temperature stabilization is critical to maintain industrial lasers at peak performance and allows high end printing systems to produce high quality prints at high run rates.

- High Powered Projectors
- Kiosks
- Metrology Instrumentation
- Digital Color Printing Systems
- Industrial Laser Systems

## Food & Beverage

Temperature control is crucial to keep food fresh and beverages cold.

- Beverage Coolers
- Small Refrigerators
- Portable Food Containers
- Coffee Makers
- Juice Dispensers
- Vending Machines







# Power Cool Series

## Liquid-to-Air Systems (LA)


Liquid-to-Air Assemblies cool or heat liquids that flow through a heat exchanger. The liquid heat exchanger is designed for a re-circulating system, absorbs heat and pumps it through the TEM, where it dissipates into the outside environment through an air heat exchanger. Specifications apply to an ambient temperature of 32°C and nominal voltage with tolerances ±10%.



| PART NO.           | COOLING POWER (W) | NOMINAL VOLTAGE (V) | CURRENT (A) | WEIGHT (kg) | DIMENSIONS (mm) |     |     |     |    |    |
|--------------------|-------------------|---------------------|-------------|-------------|-----------------|-----|-----|-----|----|----|
|                    |                   |                     |             |             | Lw              | Lc  | Ww  | Wc  | Hw | Hc |
| LA-024-12-02-00-00 | 24                | 12                  | 2.4         | 0.4         | 80              | 80  | 60  | 60  | 64 | 15 |
| LA-024-24-02-00-00 | 24                | 24                  | 2.0         | 0.4         | 80              | 80  | 60  | 60  | 64 | 15 |
| LA-045-12-02-00-00 | 43                | 12                  | 4.1         | 1.3         | 160             | 100 | 122 | 60  | 71 | 20 |
| LA-045-24-02-00-00 | 47                | 24                  | 2.8         | 1.3         | 160             | 100 | 122 | 60  | 71 | 20 |
| LA-075-24-02-00-00 | 71                | 24                  | 3.7         | 1.8         | 230             | 140 | 122 | 60  | 71 | 20 |
| LA-115-24-02-00-00 | 113               | 24                  | 5.8         | 3.0         | 300             | 240 | 152 | 60  | 78 | 20 |
| LA-160-24-02-00-00 | 160               | 24                  | 7.4         | 3.5         | 300             | 200 | 152 | 136 | 84 | 20 |

## Tunnel Series


The Tunnel Series TEAs are designed with a patented, high-performance cross flow technology that maximizes heat transfer when pulling air through a heat exchanger. The number of airflow paths required to operate is reduced when compared to traditional impingement flow TEAs. This product series is offered in 12 or 24 volt configurations and can cool by either convection or conduction means.



| PART NO.            | COOLING POWER (W) | NOMINAL VOLTAGE (V) | CURRENT (A) | DIMENSIONS (mm) |        |       |
|---------------------|-------------------|---------------------|-------------|-----------------|--------|-------|
|                     |                   |                     |             | Height          | Length | Width |
| DA-011-05-02-00-00  | 11                | 5                   | 2.2         | 56              | 60     | 44    |
| DA-033-12-02-00-00  | 32                | 12                  | 3.1         | 82              | 99     | 66    |
| ATT-027-12-22-00-00 | 27                | 12                  | 2.3         | 142             | 115    | 84    |
| AAT-032-12-22-00-00 | 33                | 12                  | 2.8         | 141             | 155    | 84    |
| AAT-055-12-22-00-00 | 56                | 12                  | 5.3         | 142             | 180    | 84    |
| ATT-055-24-22-00-00 | 55                | 24                  | 2.6         | 142             | 180    | 84    |
| AAT-085-12-22-00-00 | 82                | 12                  | 8.1         | 154             | 248    | 83    |
| AAT-085-24-22-00-00 | 85                | 24                  | 4.2         | 154             | 248    | 83    |
| DAT-029-12-02-00-00 | 29                | 12                  | 2.6         | 87              | 96     | 65    |
| DAT-040-12-02-00-00 | 40                | 12                  | 2.7         | 85              | 155    | 65    |
| DAT-065-12-02-00-00 | 65                | 12                  | 5.1         | 85              | 180    | 65    |
| DAT-065-24-02-00-00 | 64                | 24                  | 2.6         | 85              | 180    | 65    |
| DAT-105-12-02-00-00 | 103               | 12                  | 8.5         | 98              | 248    | 83    |
| DAT-105-24-02-00-00 | 106               | 24                  | 4.4         | 98              | 248    | 83    |

# Outdoor Cooler Series



The Outdoor Cooler Series is designed for outdoor use to control the temperature of electronic cabinets. The product series has been designed to pass harsh environmental demands such as earthquake resistance, salt fog, wind-driven rain, high temperature exposure and dust. The cooling capacity ranges from 100 to 250 Watts. This product series is offered in 24 and 48 VDC configurations and is designed for outdoor use in the telecom and industrial markets. As a standard option products are also sold with bi-polar thermostatic control to heat and cool to specific temperature set points.



| PART NO.            | COOLING POWER (W) | NOMINAL VOLTAGE (VDC) | CURRENT (A) | TEMPERATURE REGULATION | DIMENSIONS (mm) |        |       |
|---------------------|-------------------|-----------------------|-------------|------------------------|-----------------|--------|-------|
|                     |                   |                       |             |                        | Height          | Length | Width |
| AA-100-24-44-00-XX  | 102               | 24                    | 5.6         | Open Loop              | 180             | 300    | 122   |
| AA-100-48-44-00-XX  | 102               | 48                    | 2.8         | Open Loop              | 180             | 300    | 122   |
| AA-150-24-44-00-XX  | 143               | 24                    | 7.9         | Open Loop              | 180             | 300    | 152   |
| AA-150-48-44-00-XX  | 143               | 48                    | 3.9         | Open Loop              | 180             | 300    | 152   |
| AA-200-24-44-00-XX  | 193               | 24                    | 11.3        | Open Loop              | 183             | 400    | 153   |
| AA-200-48-44-00-XX  | 193               | 48                    | 5.6         | Open Loop              | 183             | 400    | 153   |
| AA-230-24-D44-00-XX | 230               | 24                    | 12.1        |                        | 105             | 400    | 180   |
| AA-230-48-D44-00-XX | 230               | 48                    | 6.1         |                        | 105             | 400    | 180   |
| AA-250-24-44-00-XX  | 244               | 24                    | 12.1        | Open Loop              | 204             | 400    | 153   |
| AA-250-48-44-00-XX  | 244               | 48                    | 6.1         | Open Loop              | 204             | 400    | 153   |
| AA-480-24-44-00-XX  | 480               | 24                    | 19.3        |                        | 122             | 330    | 303   |
| AA-480-48-44-00-XX  | 480               | 48                    | 6.1         |                        | 122             | 330    | 303   |

# Cascade Series



The Cascade Series is a TEA that is specifically designed to reach colder temperatures than standard TEA product offerings. The TEMs are custom designed multistage cascades that achieve a high cooling capacity (Qc) at high temperature differentials ( $\Delta T$ ). The cold side mechanism can transfer heat using convective (sink and fan) or conductive (cold plate) means. This product series is offered in 12 or 24 volt configurations and is designed for indoor use in lab instruments.



| PART NO.            | COOLING POWER | NOMINAL VOLTAGE (V) | CURRENT (A) | DIMENSIONS (mm) |        |       |
|---------------------|---------------|---------------------|-------------|-----------------|--------|-------|
|                     |               |                     |             | Height          | Length | Width |
| AAC-050-24-22-00-00 | 49            | 24                  | 4.7         | 152             | 230    | 122   |
| DAC-035-12-02-00-00 | 31            | 12                  | 4.8         | 91              | 160    | 122   |
| DAC-060-24-02-00-00 | 58            | 24                  | 4.6         | 91              | 230    | 122   |

## Direct-to-Liquid Systems (DL)

Direct-to-Liquid Assemblies cool or heat objects attached directly to the cold plate. Heat is dissipated into a liquid heat exchanger on the hot side. The liquid circuit is normally a re-circulating type that requires a pump and additional liquid heat exchanger that dissipates heat into the ambient environment. Specifications apply to the warm side liquid temperature of 32°C and nominal voltage with tolerances ±10%.



| PART NO.        | COOLING POWER (W) | NOMINAL VOLTAGE (V) | CURRENT (A) | WEIGHT (kg) | DIMENSIONS (mm) |     |    |    |    |    |
|-----------------|-------------------|---------------------|-------------|-------------|-----------------|-----|----|----|----|----|
|                 |                   |                     |             |             | Lw              | Lc  | Ww | Wc | Hw | Hc |
| DL-060-12-00-00 | 59                | 12                  | 4.2         | 0.4         | 100             | 60  | 60 | 60 | 15 | 24 |
| DL-060-24-00-00 | 59                | 24                  | 2.1         | 0.4         | 100             | 60  | 60 | 60 | 15 | 24 |
| DL-120-24-00-00 | 122               | 24                  | 4.2         | 0.7         | 140             | 120 | 60 | 60 | 15 | 24 |
| DL-210-24-00-00 | 207               | 24                  | 8.1         | 1.3         | 240             | 120 | 60 | 60 | 15 | 24 |

## Temperature Controllers

Laird offers three types of controllers to drive TEAs. The Q Series is designed for single directional thermostatic control. The PR Series is designed for PID control and comes with GUI to make adjustments on the fly. Bi-polar thermostatic controllers are available, but sold with Outdoor Cooler Series units only.



| PART NO. | DESCRIPTION                     | REGULATION TYPE | TEMP RANGE (°C)          | ACCURACY (°C)    | INPUT VOLTAGE | MAX OUTPUT CURRENT                 | ALARM OUTPUTS |
|----------|---------------------------------|-----------------|--------------------------|------------------|---------------|------------------------------------|---------------|
| SR-54    | Microcontroller based device    | ON/OFF or PID   | -20 to 100°C             | ±0.13°C          | 16 to 60 VDC  | 20 Amps, 28 VDC<br>12 Amps, 60 VDC | Yes           |
| PR-59    | Programmable PID Controller     | PWM             | Sensor Dependent         | Sensor Dependent | 11-30VDC      | < 15A                              | Yes           |
| QC-50    | Single Directional Thermostatic | ON/OFF          | Cool >5°C<br>Off <2 °C   | ±1.0°C           | 11-58VDC      | < 16A                              | Yes           |
| QE-50    | Single Directional Thermostatic | ON/OFF          | Cool >35°C<br>Off <32 °C | ±1.0°C           | 11-58VDC      | < 16A                              | Yes           |

## MRC Series Recirculating Thermoelectric Chillers

MRC Chillers are self contained re-circulating chillers that offer dependable, compact performance by controlling the temperature of a coolant in a liquid circuit. The coolant is re-circulated using a pump with high mean time between failures (MTBF). Heat from the coolant is absorbed by a heat exchanger and dissipated through high density heat sinks equipped with brand name fans. The TEMs are custom designed to achieve long life operation. The unit is regulated with an easy-to-use digital temperature controller and is housed inside an aesthetic sheet metal casing.



| MODEL               | COOLING CAPACITY (dT=12°C) | FLOW RATE (@ 4 bar) | HEATING OPTION | WEIGHT (kg) | HEIGHT (in) | WIDTH (in) | DEPTH (in) |
|---------------------|----------------------------|---------------------|----------------|-------------|-------------|------------|------------|
| MRC 150,DH2,DVA     | 151 watts<br>515 Btu/hr    | 2.9 lpm             | No             | 10.9        | 12.2        | 7.8        | 15.2       |
| MRC 300,DH2,DVA     | 299 watts<br>1020 Btu/hr   | 3.3 lpm             | No             | 13.6        | 15.4        | 8.4        | 13.3       |
| MRC 150,DH2,HT, DVA | 151 watts<br>515 Btu/hr    | 2.9 lpm             | Yes            | 10.9        | 12.2        | 7.8        | 15.2       |
| MRC 300,DH2,HT, DVA | 299 watts<br>1020 Btu/hr   | 3.3 lpm             | Yes            | 13.6        | 15.4        | 8.4        | 13.3       |



## Customization

Since there are so many unique attributes that need to be ascertained for each application, often a customized TEA will yield a more optimal thermal solution. Laird offers strong engineering services with a global presence that supports onsite concept generation, thermal modeling, thermal design and rapid prototyping. We also offer validation test services to meet unique compliance standards for each industry, such as Telcordia, MIL-STDs or unique standards specific to a medical, automotive or industrial account. Minimum order quantity (MOQ) applies for all custom TEA designs and validation testing. Contact Laird today to support your customization needs.

**On Sight Concept Generation**

**Mechanical Design Support**



**Thermal Modeling Analysis**

**Temperature Control Design**

**Prototype Development**

**Validation Testing**

**Regional Manufacturing Capabilities**



Smart Technology. Delivered.™

Americas: +1.919.597.7300

Europe: +46.31.420530

Asia: +86.755.2714.1166

[www.lairdtech.com](http://www.lairdtech.com)

### THR-BRO-THERMOELECTRIC-ASSEMBLIES 022818

Any information furnished by Laird, Inc. and its agents is believed to be accurate and reliable. All specifications are subject to change without notice. Responsibility for the use and application of Laird materials rests with the end user, since Laird and its agents cannot be aware of all potential uses. Laird makes no warranties as to the fitness, merchantability or suitability of any Laird materials or products for any specific or general uses. Laird shall not be liable for incidental or consequential damages of any kind. All Laird products are sold pursuant to the Laird Terms and Conditions of sale in effect from time to time, a copy of which will be furnished upon request. © Copyright 2016 Laird, Inc. All Rights Reserved. Laird, the Laird Logo and other marks are trademarks or registered trademarks of Laird, Inc. or an affiliate company thereof. Other product or service names may be the property of third parties. Nothing herein provides a license under any Laird or any third party intellectual property rights.