

Chipsmall Limited consists of a professional team with an average of over 10 year of expertise in the distribution of electronic components. Based in Hongkong, we have already established firm and mutual-benefit business relationships with customers from, Europe, America and south Asia, supplying obsolete and hard-to-find components to meet their specific needs.

With the principle of "Quality Parts, Customers Priority, Honest Operation, and Considerate Service", our business mainly focus on the distribution of electronic components. Line cards we deal with include Microchip, ALPS, ROHM, Xilinx, Pulse, ON, Everlight and Freescale. Main products comprise IC, Modules, Potentiometer, IC Socket, Relay, Connector. Our parts cover such applications as commercial, industrial, and automotives areas.

We are looking forward to setting up business relationship with you and hope to provide you with the best service and solution. Let us make a better world for our industry!



### Contact us

Tel: +86-755-8981 8866 Fax: +86-755-8427 6832

Email & Skype: info@chipsmall.com Web: www.chipsmall.com

Address: A1208, Overseas Decoration Building, #122 Zhenhua RD., Futian, Shenzhen, China









# DS9100 Touch and Hold Probe Stampings

#### www.maxim-ic.com

#### **FEATURES**

- Compact two-piece, all-metal receptacle for F5 MicroCan
- Accepts two-thirds of the MicroCan (onethird of MicroCan will extend out)
- Allows reading <u>i</u>Buttons® with either momentary or dwelled contact
- Outer ring will hold MicroCan for dwelled contact
- Two options for data contact: cantilever (DS9100B) or coiled spring (DS9100C)
- >10000 insertion/withdrawal cycles with no performance degradation
- Redundancy of contacts and high contact force ensure reliability
- Probe withstands high temperatures required for PCB solder reflow operations
- Material is stainless steel with selective tinlead plating for optimal solderability to printed circuit board
- Cleaning fluids drain freely for quick clean up


#### ORDERING INFORMATION


PART	DESCRIPTION
DS9100-A+	Outer Contact (Ground)
DS9100-B+	Center Contact Cantilever
	(Data)
DS9100-C+	Center Contact Coiled Spring
	(Data)

 $<sup>+</sup>Denotes\ a\ lead(Pb)$ -free/RoHS-compliant package.

iButton is a registered trademark of Maxim Integrated Products, Inc.

#### **DS9100A WITH DS9100B**






Dimensions are in millimeters

## DS9100C WITH CORRECT ORIENTATION TO SOLDER PAD







#### DESCRIPTION

The DS9100 Touch and Hold Probe Stampings' function is similar to the DS9098 <u>i</u>Button Retainer. An F5 MicroCan will fit completely into the DS9098, but the flange and about one-third of the can will extend out if pressed into the DS9100. As a probe, the DS9100A together with the coiled spring DS9100C allows reading <u>i</u>Buttons on contact. With additional pressure, the stiff springs of the DS9100A's outer ring will deflect and grip the MicroCan sufficiently to provide a continuous contact to both the can rim (ground) and the can lid (data). If reading on contact is not required, the cantilever type center contact DS9100B can be used rather than the DS9100C.


#### PRINTED CIRCUIT BOARD LAYOUTS






Compatible PCB layout.


Good for either center part DS9100B or DS9100C




Additional diminsions for ground contact.


CENTER-DATA OUTER RING-GROUND COPPER CLADDING>0.3 kg/m $^2$  or > 34  $\mu$ m (>1 oz/sq. ft)





Center piece optimized for cantilever DS9100B





Center piece optimized for coiled spring DS9100C

Dimensions are in millimeters.

The DS9100 stampings are mounted on Side A of the printed circuit board.

#### **REVISION HISTORY**

REVISION DATE	DESCRIPTION	PAGES CHANGED
8/09	Updated the PART numbers in the <i>Ordering Information</i> table to indicate lead(Pb)-free/RoHS-compliant packages.	1