

Chipsmall Limited consists of a professional team with an average of over 10 year of expertise in the distribution of electronic components. Based in Hongkong, we have already established firm and mutual-benefit business relationships with customers from, Europe, America and south Asia, supplying obsolete and hard-to-find components to meet their specific needs.

With the principle of "Quality Parts, Customers Priority, Honest Operation, and Considerate Service", our business mainly focus on the distribution of electronic components. Line cards we deal with include Microchip, ALPS, ROHM, Xilinx, Pulse, ON, Everlight and Freescale. Main products comprise IC, Modules, Potentiometer, IC Socket, Relay, Connector. Our parts cover such applications as commercial, industrial, and automotives areas.

We are looking forward to setting up business relationship with you and hope to provide you with the best service and solution. Let us make a better world for our industry!



Contact us

Tel: +86-755-8981 8866 Fax: +86-755-8427 6832

Email & Skype: info@chipsmall.com Web: www.chipsmall.com

Address: A1208, Overseas Decoration Building, #122 Zhenhua RD., Futian, Shenzhen, China










DATASHEET

Infrared Receiver Module EAIRMBA1 & EAIRMBA3 & EAIRMBA6



Pin Configuration

- 1. OUT
- $2. V_{CC}$
- 3. GND



Block Diagram

Features

- · High protection ability against EMI
- · Circular lens for improved reception characteristics
- · Available for various carrier frequencies
- · Min burst length: 8 cycles
- Min gap length: 12 cycles
- · Low operating voltage and low power consumption
- · High immunity against ambient light
- · High immunity against TFT and PDP backlight
- · Long reception range
- · High sensitivity
- Pb free and RoHS compliant
- · Compliance with EU REACH
- Compliance Halogen Free .(Br <900 ppm , Cl <900 ppm , Br+Cl < 1500 ppm)

Description

The EAIRMBA1 & EAIRMBA3 & EAIRMBA6 devices are DIP type infrared receivers which have been developed and designed by using the latest IC technology.


The PIN diode and preamplifier are assembled onto a lead frame and molded into a black epoxy package which operates as an IR filter. The demodulated output signal can directly be decoded by a microprocessor..

Applications

- AV equipment such as TV, VCR, DVD, CD, MD, etc.
- · CATV set top boxes
- Multi-media Equipment
- · Other devices using IR remote control



Application Circuit



The RC Filter must be connected as close as possible to Vcc and GND pins

Parts Table

Model No.	Carrier Frequency		
EAIRMBA1	36 kHz		
EAIRMBA3	38 kHz		
EAIRMBA6	56 kHz		

Absolute Maximum Ratings (Ta=25℃)

Parameter	Symbol	Rating	Unit
Supply Voltage	Vcc	6	V
Operating Temperature	Topr	-20 ~ +80	$^{\circ}\! \mathbb{C}$
Storage Temperature	Tstg	-40 ~ +85	$^{\circ}\! {\mathbb C}$
Soldering Temperature *1	Tsol	260	$^{\circ}$ C

^{*1} 4mm from mold body for less than 10 seconds



Electro-Optical Characteristics (Ta=25℃,Vcc=3V)

Parameter	Symbol	Min.	Тур.	Max.	Unit	Condition
Current consumption	Icc		0.4	0.6	mA	No input signal
Supply voltage	V _{CC}	2.7	-	5.5	V	
Peak wavelength	λ_{p}		940		nm	
Reception range	L ₀	14				
	L ₄₅	6			– m	See chapter
Half angle(horizontal)	ϕ_{h}		±35		deg ,Test method'	
Half angle(vertical)	φν		±35		deg	
High level pulse width	T _H	450		750	μs	Test signal
Low level pulse width	T _L	450		750	μs	according to figure 1
High level output voltage	V _{OH}	Vcc-0.4			V	No load
Low level output voltage	V _{OL}		0.2	0.5	V	I _{SINK} ≦2mA
Internal pull up resistor	R_{PU}	34	40	46	kΩ	



Test method


The specified electro-optical characteristics are valid under the following conditions.


- 1. Measurement environment
 - A place without extreme light reflections.
- 2. External light

The environment contains an ordinary, white fluorescent lamp without high frequency modulation. The color temperature is 2856K and the illumination at the IR receiver is less than 10 Lux (Ev≤10Lux).

- 3. Standard transmitter
 - The test transmitter is calibrated by using the circuit shown in figure 2. The radiation intensity of the transmitter is adjusted until **Vo=400mVp-p.** Both, the test transmitter and the photo diode, have a peak wavelength of 940nm. The photo diode for calibration is PD438B (λp=940nm, Vr=5V).
- 4. The measurement system is shown in Fig.-3

Fig.-1 Transmitter Wave Form







٧он IRM output signal

Fig.-2 standard transmitter calibration


Fig.-3 Measuring System








Typical Electro-Optical Characteristics Curves





Package Dimension (Dimensions in mm)






Code information

Protocol	Suitable	Protocol	Suitable
JVC	Yes	RCA	No
Matsushita	Yes	Sharp	Yes
Mitsubishi	No	Sony 12 Bit	Yes
NEC	Yes	Sony 15 Bit	No
RC5	Yes	Sony 20Bit	No
RC6	Yes	Toshiba	Yes
RCMM	No	Zenith	Yes
RCS-80	No	Continuous Code	No

Device Marking



Notes

- 1 denotes Year code
- 2 denotes Month code
- 3 denotes Device number
- 4 denotes Carrier frequency

Packing Quantity

1500 pcs / Box 10 Boxes / Carton



Application Restrictions

- 1. Above specification may be changed without notice. Everlight Americas will reserve authority on material change for above specification.
- 2. When using this product, please observe the absolute maximum ratings and the instructions for use outlined in these specification sheets. Everlight Americas assumes no responsibility for any damage resulting from use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
- 3. These specification sheets include materials protected under copyright of Everlight Americas. Reproduction in any form is prohibited without the specific consent of Everlight Americas.