



Chipsmall Limited consists of a professional team with an average of over 10 year of expertise in the distribution of electronic components. Based in Hongkong, we have already established firm and mutual-benefit business relationships with customers from,Europe,America and south Asia,supplying obsolete and hard-to-find components to meet their specific needs.

With the principle of “Quality Parts,Customers Priority,Honest Operation,and Considerate Service”,our business mainly focus on the distribution of electronic components. Line cards we deal with include Microchip,ALPS,ROHM,Xilinx,Pulse,ON,Everlight and Freescale. Main products comprise IC,Modules,Potentiometer,IC Socket,Relay,Connector.Our parts cover such applications as commercial,industrial, and automotives areas.

We are looking forward to setting up business relationship with you and hope to provide you with the best service and solution. Let us make a better world for our industry!




Contact us

Tel: +86-755-8981 8866 Fax: +86-755-8427 6832

Email & Skype: info@chipsmall.com Web: www.chipsmall.com

Address: A1208, Overseas Decoration Building, #122 Zhenhua RD., Futian, Shenzhen, China





Shuttle click

PID: MIKROE-2880

Weight: 25 g

One click board™, numerous possibilities


Shuttle click is a mikroBUS™ socket expansion board, which provides an easy and elegant solution for stacking up to four click boards™ on a single mikroBUS™. It is a perfect solution for expanding the capacity of the development system with additional mikroBUS™ sockets when there is a demand for using more click boards™ than the used development system is able to support.

Shuttle click can be especially interesting for the development systems that are equipped with a very small number of mikroBUS™ slots, such as the Clicker family of development systems. Using Shuttle click on such system will greatly improve its usability by adding more mikroBUS™ sockets, yet it will remain small, compact and manageable.

How does it work?

Shuttle click consists of a high-quality PCB that can be connected to the mikroBUS™ as any other click board. The central part of the Shuttle click is populated with the four ICD BOX headers. Each of these four headers is used to connect to the same type of header on the add-on board, also known as mikroBUS Shuttle, by a flat ribbon cable. Thanks to the ICD BOX headers, the connection remains firm and stable. Besides the ICD BOX headers, these mikroBUS Shuttle add-on boards also have one mikroBUS™ equipped, so that the click board can be securely fitted to it. Having this kind of stacking topology, allows for easy manipulation and reconfiguration of the stacked click boards™, retaining a perfect connection quality at all times.

When there's a need to expand the development system with even more mikroBUS™ slots, one of the free mikroBUS shuttles can be populated with yet another Shuttle click, allowing even more connections. This makes the stacking capacity almost unlimited. However, attention should be paid not to make mikroBUS™ lines too long. In situations like this, the frequency of the communication might need to be stepped down a bit, in order to compensate for the longer mikroBUS™ signal lines.



Lines of the mikroBUS™ to which Shuttle click is attached, are shared through all four ICD BOX headers - each of the four ICD BOX 2x8 pin headers mirrors pins of the connected mikroBUS™. Therefore, each mikroBUS Shuttle add-on board shares the same mikroBUS™ pins as the other mikroBUS Shuttles connected to the same Shuttle click. For this reason, an extra care should be taken when working with click boards™ that share the same pins on the mikroBUS™, either for the communication (SPI, UART, I2C) or for some other purpose (RST, INT, or other pins used as GPIO). For example, I2C and 1-Wire protocols are designed with stacking in mind, so the collision avoidance mechanisms are already in place for these protocols. It is enough to change the slave address of the click board™ and data collision won't be a problem anymore, even while sharing the same pins for the communication.

Also, since all the stacked click boards™ share the same power rails, a care should be taken when combining click boards™ with significant power consumption. The power consumption from all the click boards™ combined should not exceed the maximum power that a development system can deliver.

Click board™ product range

The union of Shuttle click, mikroBUS Shuttle and click boards™ allows you to reach an unlimited number possibilities when it comes to combining different functionalities. You just need to choose the ones you want from our ever-growing range: environmental sensors, LEDs, speech recognition, heart rate sensors, motor control, GSM, GPS, WiFi, analog to digital converters, movement sensors.

More than 400 click boards™ that can be stacked and integrated in a simple and convenient way are at your disposal.


Turn your development system into a mikroBUS shuttle station!

Specifications

Type	Adapter
Applications	Provides easy, secure and reliable stacking of up to four additional boards per mikroBUS™ socket.
Interface	GPIO
Input Voltage	3.3V,5V
Click board size	L (57.15 x 25.4 mm)

Pinout diagram

This table shows the pinout on the mikroBUS™ socket.

Notes					Notes
Analog Input	1	AN	PWM	16	PWM Output
Reset	2	RST	INT	15	Hardware Interrupt

SPI Chip Select	3	CS	RX	14	UART Receive
SPI Clock	4	SCK	TX	13	UART Transmit
SPI Master Input Slave Output	5	MISO	SCL	12	I2C Clock
SPI Master Output Slave Input	6	MOSI	SDA	11	I2C Data
Power Supply	7	3.3V	5V	10	Power Supply
Ground	8	GND	GND	9	Ground

Onboard settings and indicators

Label	Name	Default	Description
J1	HM2X8	-	J1 Connector (IDC BOX header) has 16 pins, one for every mikroBUS™ pin. Flat ribbon cable provides connection to mikroBUS™ Shuttle which has the same type of connector.
J2	HM2X8	-	J2 Connector (IDC BOX header) has 16 pins, one for every mikroBUS™ pin. Flat ribbon cable provides connection to mikroBUS™ Shuttle which has the same type of connector.
J3	HM2X8	-	J3 Connector (IDC BOX header) has 16 pins, one for every mikroBUS™ pin. Flat ribbon cable provides connection to mikroBUS™ Shuttle which has the same type of connector.
J4	HM2X8	-	J4 Connector (IDC BOX header) has 16 pins, one for every mikroBUS™ pin. Flat ribbon cable provides connection to mikroBUS™ Shuttle which has the same type of connector.

Downloads

[mikroBUS™ standard specifications](#)

[Shuttle click schematic](#)

[Shuttle click - 2D and 3D click](#)