mail

Chipsmall Limited consists of a professional team with an average of over 10 year of expertise in the distribution of electronic components. Based in Hongkong, we have already established firm and mutual-benefit business relationships with customers from, Europe, America and south Asia, supplying obsolete and hard-to-find components to meet their specific needs.

With the principle of "Quality Parts, Customers Priority, Honest Operation, and Considerate Service", our business mainly focus on the distribution of electronic components. Line cards we deal with include Microchip, ALPS, ROHM, Xilinx, Pulse, ON, Everlight and Freescale. Main products comprise IC, Modules, Potentiometer, IC Socket, Relay, Connector. Our parts cover such applications as commercial, industrial, and automotives areas.

We are looking forward to setting up business relationship with you and hope to provide you with the best service and solution. Let us make a better world for our industry!



Contact us

Tel: +86-755-8981 8866 Fax: +86-755-8427 6832 Email & Skype: info@chipsmall.com Web: www.chipsmall.com Address: A1208, Overseas Decoration Building, #122 Zhenhua RD., Futian, Shenzhen, China





General Purpose Strain Gages - Linear Pattern

GAGE PATTERN DATA								
•		٦			GAGE DESIGNATI	ON	RESISTAN (OHMS)	
	/			See Note	1		See Note 2	
-		actual size		CEA-XX-250U\ CEA-XX-250U\ CEA-XX-250U\ CEA-XX-250U\	N-175 N-350	120 ± 0.3 175 ± 0.3 350 ± 0.3 1000 ± 0.3	% P2 % P2	
		4			DESCRIPTIO General-purpo 0.07 in [2.5 x 1	se gage		older tab area 0.10 x DUN pattern.
GAGE DIMENSIONS		Legend: ES = Each Section S = Section (S1						
Gage Length	Overall Length	Grid \	Width	Ov	erall Width	Matr	ix Length	Matrix Width
0.250	0.450	0.1	0.180		0.180		0.55	0.27
6.35	11.43	4.5	57		4.57		14.0	6.9

GAGE SERIES DATA See Gage Series data sheet for complete specifications.							
Series	Description	Strain Range	Temperature Range				
CEA	Universal general-purpose strain gages.	±5%	-100° to +350°F [-75° to +175°C]				

Note 1: Insert desired S-T-C number in spaces marked XX.

Note 2: Products with designations and options shown in bold are not RoHS compliant.