

Chipsmall Limited consists of a professional team with an average of over 10 year of expertise in the distribution of electronic components. Based in Hongkong, we have already established firm and mutual-benefit business relationships with customers from, Europe, America and south Asia, supplying obsolete and hard-to-find components to meet their specific needs.

With the principle of "Quality Parts, Customers Priority, Honest Operation, and Considerate Service", our business mainly focus on the distribution of electronic components. Line cards we deal with include Microchip, ALPS, ROHM, Xilinx, Pulse, ON, Everlight and Freescale. Main products comprise IC, Modules, Potentiometer, IC Socket, Relay, Connector. Our parts cover such applications as commercial, industrial, and automotives areas.

We are looking forward to setting up business relationship with you and hope to provide you with the best service and solution. Let us make a better world for our industry!



## Contact us

Tel: +86-755-8981 8866 Fax: +86-755-8427 6832

Email & Skype: info@chipsmall.com Web: www.chipsmall.com

Address: A1208, Overseas Decoration Building, #122 Zhenhua RD., Futian, Shenzhen, China











spectrasymbol

MAGNETOPOT PATENT PENDI

# MAGNETOPOT MP1

#### **Features**

- Contactless Linear Sensor
- IP64 Debris Proof, Splash Proof
- Ideal for Hydraulic and Pneumatic Position Sensing
- Liquid Level Capability
- Upon request
  - Male or Female Nicomatic Connectors
  - Corresponding Exterior Magnet

#### **Mechanical Specifications**

- -Life Cycle: >1 million -Height: ≤3.50mm (0.138")
- -Actuation Force: 0.09 to 0.11 lbs pull force at desired distance (pull force rating is for the exterior magnet using a test plate of cold rolled steel).

#### **Environmental Specifications**


-Operating Temperature: up to +85°C -IP Rating of Active Area: IP64

#### **Electrical Specifications**


- -Resistance Standard: 10k Ohms (lengths >300mm = 20k Ohms)
- -Resistance Custom: 5k to 500k Ohms
- -Resistance Tolerance: ±20%
- -Effective Electrical Travel: 8 to 1200mm
- -Resolution: Depends on the exterior magnet strength and distance to the MagnetoPot
- -Power Rating: 0.50 Watt continuous, 1 Watt Peak
- -Dielectric Value: No affect @ 500VAC for 1 minute
- -Independent Linearity: ±5% (±1% available)
- -Hysteresis: 3mm\*


\*Please note that the hysteresis is directly affected by the drive magnet size, strength, and distance from the internal magnet.

### Dimensional Diagram - Stock Linear MagnetoPots



А	12.50mm	25.00mm	50.00mm	100.00mm	150.00mm	171.89mm	200.00mm	300.00mm	400.00mm	500.00mm	750.00mm	1000.00mm
	0.492"	0.984"	1.969"	3.937"	5.906"	6.768"	7.874"	11.811"	15.748"	19.685"	29.528"	39.370"
Р	28.36mm	40.86mm	65.86mm	115.86mm	165.86mm	185.86mm	215.86mm	315.86mm	415.86mm	515.86mm	765.86mm	1015.86mm
	1.117"	1.609"	2.593"	4.562"	6.531"	7.318"	8.499"	12.436"	16.373"	20.310"	30.153"	39.995"
Т	12.70mm 0.500"		24.89mm 0.980"									





#### Customization

Customize the size and shape. Such custom requests, for example, can be: custom lengths 10mm-1200mm; custom rotary diameters, etc. Spectra Symbol would be glad to quote your custom application, just contact us at sales@spectrasymbol.com or (888)795-2283.

#### How It Works

The MagnetoPot is simple, yet elegant in its ability to track motion in a contactless manner. A magnet on the inside of a cylinder, or a magnet on the opposing side of a motion device will guide the built-in magnetics of the MagnetoPot for position location through a potentiometric output.

The MagnetoPot is a sealed potentiometer, in the membrane potentiometer tradition, yet it does not require a wiper/actuator to connect the collector and the resistor. Instead, the MagnetoPot is controlled by an outside magnet, which attracts the magnetic forces within the MagnetoPot to connect to the linear resistor and give linear potentiometer feedback.

The wiper inside the sealed pot is magnetic or ferromagnetic, and will only perform if connected with an exterior magnet.

As opposed to a magnetically-based Reed Switch, which gives simply "open" or "close" signals, the MagnetoPot gives the full linear travel of a hydraulic or pneumatic cylinder.

In liquid level applications, the MagnetoPot can attach to the outside of a liquid tank and give position of the magnet inside the float. No water ingress, no wearing of the part by environment, because the MagnetoPot is outside of the tank.

#### **Design and Contruction**

The MagnetoPot is made of polyester, fiberglass and kapton, depending on the specification required. It functions as a voltage divider, a resistor or rheostat, as desired by the end-user. By bringing the exterior magnet into a proximity necessary to connect with the internal magnetic attractors, the operator can obtain linear position sensing based on the location of the exterior magnet. As the exterior magnet moves, so does the electrical output of the MagnetoPot.

The MagnetoPot should not be mounted to a ferromagnetic surface.

