



Chipsmall Limited consists of a professional team with an average of over 10 year of expertise in the distribution of electronic components. Based in Hongkong, we have already established firm and mutual-benefit business relationships with customers from,Europe,America and south Asia,supplying obsolete and hard-to-find components to meet their specific needs.

With the principle of “Quality Parts,Customers Priority,Honest Operation,and Considerate Service”,our business mainly focus on the distribution of electronic components. Line cards we deal with include Microchip,ALPS,ROHM,Xilinx,Pulse,ON,Everlight and Freescale. Main products comprise IC,Modules,Potentiometer,IC Socket,Relay,Connector.Our parts cover such applications as commercial,industrial, and automotives areas.

We are looking forward to setting up business relationship with you and hope to provide you with the best service and solution. Let us make a better world for our industry!



Contact us

Tel: +86-755-8981 8866 Fax: +86-755-8427 6832

Email & Skype: info@chipsmall.com Web: www.chipsmall.com

Address: A1208, Overseas Decoration Building, #122 Zhenhua RD., Futian, Shenzhen, China



Tack Flux No-Clean in 30cc Syringe

Product Highlights

- Ideal for all rework, solder, de-solder and reflow applications
- Non-corrosive, non-conductive, no-clean
- Tack flux will not run all over PCB when applied
- Has a pleasant odor
- Excellent wetting
- Easily cleaned with isopropyl alcohol (IPA)
- Attachment of BGA spheres
- Soldering flip chip components
- Long stencil life
- Wide process window
- Clear residue
- Can be used with Leaded and Lead-Free applications
- RoHS II and REACH compliant

Specifications

Flux Type:	Synthetic No-Clean (for Leaded and Lead-Free applications)
Flux Classification:	RELO
Packaging:	30cc/30g Syringe
Shelf Life:	Refrigerated >24 months, Unrefrigerated >24 months

Stencil Life

- >8 hours @ 20-50% RH 22-28°C (72-82°F)
- >4 hours @ 50-70% RH 22-28°C (72-82°F)

Stencil Cleaning

Automated stencil cleaning systems for both stencil and misprinted boards. Manual cleaning using isopropyl alcohol (IPA).

Storage and Handling

Store refrigerated or at room temperature 3-25°C (37-77°F). Do not freeze. Allow 4 hours for flux to reach an operating temperature of 20-25°C (68-77°F) before use.

Conforms to the following Industry Standards:

J-STD-004B, Amendment 1 (Solder Fluxes):	Yes
RoHS 2 Directive 2011/65/EU:	Yes