



Chipsmall Limited consists of a professional team with an average of over 10 year of expertise in the distribution of electronic components. Based in Hongkong, we have already established firm and mutual-benefit business relationships with customers from,Europe,America and south Asia,supplying obsolete and hard-to-find components to meet their specific needs.

With the principle of "Quality Parts,Customers Priority,Honest Operation,and Considerate Service",our business mainly focus on the distribution of electronic components. Line cards we deal with include Microchip,ALPS,ROHM,Xilinx,Pulse,ON,Everlight and Freescale. Main products comprise IC,Modules,Potentiometer,IC Socket,Relay,Connector.Our parts cover such applications as commercial,industrial, and automotives areas.

We are looking forward to setting up business relationship with you and hope to provide you with the best service and solution. Let us make a better world for our industry!



Contact us

Tel: +86-755-8981 8866 Fax: +86-755-8427 6832

Email & Skype: info@chipsmall.com Web: www.chipsmall.com

Address: A1208, Overseas Decoration Building, #122 Zhenhua RD., Futian, Shenzhen, China



WXP 90 Set

Product no.: T0052922599N



Benefits

- › High flexibility thanks to quick changeable heating element and tip
- › Very fast and precise reach of soldering temperature
- › Slim iron design
- › For all purpose soldering jobs
- › High mass tips for ambitious solder tasks


For this purpose, we recommend:



Solder fume extractors



Pre-heating plates



Cleaning




Soldering tips



Technical Data

Active Tip heating element technology	---
Power Response heating element technology	on
Silver Line heating element technology	---
Voltage	24 V
Power	90 W
Tip range	XNT, THM
Supply unit	WX 1, WX 2, WXA 2, WXD 2, WXR 3
WX-compatible	on
Temperature range °C	100 - 450
Temperature range °F	200 - 850
Heating time	7
Safety rest	WDH 51 (T0051517199N)
Safety rest (optional)	---
Barrel	T0058768724
Integrated direct extraction	FE attachment with tube Ø 4, 5 mm

Owning the bench



PROFESSIONAL



FILTRATION



EREM



XCELITE