

Chipsmall Limited consists of a professional team with an average of over 10 year of expertise in the distribution of electronic components. Based in Hongkong, we have already established firm and mutual-benefit business relationships with customers from, Europe, America and south Asia, supplying obsolete and hard-to-find components to meet their specific needs.

With the principle of "Quality Parts, Customers Priority, Honest Operation, and Considerate Service", our business mainly focus on the distribution of electronic components. Line cards we deal with include Microchip, ALPS, ROHM, Xilinx, Pulse, ON, Everlight and Freescale. Main products comprise IC, Modules, Potentiometer, IC Socket, Relay, Connector. Our parts cover such applications as commercial, industrial, and automotives areas.

We are looking forward to setting up business relationship with you and hope to provide you with the best service and solution. Let us make a better world for our industry!



Contact us

Tel: +86-755-8981 8866 Fax: +86-755-8427 6832

Email & Skype: info@chipsmall.com Web: www.chipsmall.com

Address: A1208, Overseas Decoration Building, #122 Zhenhua RD., Futian, Shenzhen, China









RW-2500-3 Revision 3 Page 1 of 5 August 2015

Specification RW-2500-3 TE 108-121006

THIN-WALL MARKER SLEEVES TW-TMS

Approved Signatories:

This document is electronically reviewed and approved by TE Connectivity.



RW-2500-3 Revision 3 Page 2 of 5 August 2015

1. REVISION HISTORY

Revision Number	Description of change	Date	Incorporated By
1	AFC 256	14/04/04	Alan Kean
2	AFC 372	14/04/04	Alan Kean
3	Refer to PCN	16/07/14 issued 08-2015	Lee Smith

2. SCOPE

This specification sheet, when used with RW-2500, defines the product characteristics and performance of TE Connectivity Thin-Wall Marker Sleeves.

The printing system developed for this marker sleeve is now obsolete. TE can only guarantee the physio-chemical nature of the product, and not any marking applied using non-recommended printing systems. Where non-standard systems are used, customers are required to carry out their own validation testing.

3. REQUIREMENTS

3.1. MATERIAL

The sleeving shall be fabricated from irradiated, thermally stabilized, modified polyvinylidene fluoride compound. It shall be homogeneous and essentially free from flaws, defects, pinholes, bubbles, seams, cracks or inclusions.

3.2. COLOR

The sleeves shall be supplied in white, unless otherwise specified.

3.3. PROPERTIES


The sleeves shall meet the requirements of Table 3.

3.4. FORM

The sleeves shall be cut lengths in accordance with Table 1.



RW-2500-3 Revision 3 Page 3 of 5 August 2015



Dimensions are in inches

Figure 1



RW-2500-3 Revision 3 Page 4 of 5 August 2015

TABLE 1 Sleeve Dimensions

	As Supplied			Recovered				
Product Description	Inside Diameter Minimum		Marking Length Minimum		Inside Diameter Maximum		Wall Thickness	
	in.	mm.	in.	mm.	in.	mm.	in.	mm.
TW-TMS-3/32-1.50	.093	2.36	1.60	39.41	.030	0.76	.017 <u>+</u> .003	0.43 <u>+</u> 0.08
TW-TMS-1/8-1.50	.125	3.17	1.60	39.41	.050	1.27	.017 <u>+</u> .003	0.43 <u>+</u> 0.08
TW-TMS-3/16-1.50	.187	4.74	1.57	38.65	.093	2.36	.018 <u>+</u> .003	0.46 <u>+</u> 0.08
TW-TMS-1/4-1.50	.250	6.35	1.55	38.14	.125	3.17	.018 <u>+</u> .003	0.46 <u>+</u> 0.08
TW-TMS-3/32-1.75	.093	2.36	1.90	47.00	.030	0.76	.017 <u>+</u> .003	0.43 <u>+</u> 0.08
TW-TMS-1/8-1.75	.125	3.17	1.90	47.00	.050	1.27	.017 <u>+</u> .003	0.43 <u>+</u> 0.08
TW-TMS-3/16-1.75	.187	4.74	1.85	45.70	.093	2.36	.018 <u>+</u> .003	0.46 <u>+</u> 0.08
TW-TMS-3/16-OX-1.75	.187	4.74	1.85	45.70	.062	1.57	.022 <u>+</u> .003	0.55 <u>+</u> 0.08
TW-TMS-1/4-1.75	.250	6.35	1.81	44.70	.125	3.17	.018 <u>+</u> .003	0.46 <u>+</u> 0.08
TW-TMS-1/4-OX-1.75	.250	6.35	1.81	44.70	.093	2.36	.022 <u>+</u> .003	0.56 <u>+</u> 0.08

TABLE 2

Mandrel Dimensions for Heat Shock, Heat Aging and Low Temperature Flexibility

Tubing Size	Mandrel	Mandrel Diameter		
Tubing Size	in	mm		
3/32 through 3/16	5/16	7.9		
1/4 through 3/4	3/4	19.0		



RW-2500-3 Revision 3 Page 5 of 5 August 2015

TABLE 3 Requirements

PROPERTY	UNIT	REQUIREMENT	RW-2500 TEST METHOD
PHYSICAL			
Dimensions	Inches	In accordance with Table 1	
Dimensional Recovery 3 minutes at 200°C (392°F)	Inches	In accordance with Table 1	RW-2500 Section 4.3.1.1
Longitudinal Change 3 minutes at 200°C (392°F)	Percent	10 maximum	ASTM D 2671
Tensile Strength	MPa (psi)	10.3 (1500) minimum	RW-2500 Section 4.3.2.1 ASTM D 2671
Ultimate Elongation	Percent	200 minimum	2 inches/minute
Specific Gravity		1.38 maximum	RW-2500 Section 4.3.3 ASTM D 2671
Low Temperature Flexibility 4 hours at -55°C (-67°F)		No cracking	RW-2500 Section 4.3.5.1
Heat Shock 4 hours at 250°C (482°F)		No dripping, flowing, or cracking	RW-2500 Section 4.3.6.1
Heat Aging 168 hours at 175°C (347°F)		No cracking	RW-2500 Section 4.3.7.1
Copper Contact Corrosion 16 hours at 150°C (302°F)		No pitting or blackening of copper	RW-2500 Section 4.3.14.1
Pull-Off Force			
Size: 3/32	N (Pounds)	26 (6.0) maximum	RW-2500 Section
Size: 1/8	N (Pounds)	31 (7.0) maximum	4.3.8
Size: 3/16	N (Pounds)	35 (8.0) maximum	4.3.0
Size: 1/4	N (Pounds)	40 (9.0) maximum	
ELECTRICAL Dielectric Strength	kV/mm (V/mil)	19.7 (500) minimum	RW-2500 Section 4.3.11.1 ASTM D 2671 RW-2500 Section
Volume Resistivity	ohm-cm	10 ¹⁴ minimum	4.3.12.1 ASTM D 2671
CHEMICAL Corrosive Effect 16 hours at 150°C (302°F)		Non Corrosive	RW-2500 Section 4.3.13.1 ASTM D 2671
Flammability (FED-STD-228)		Burn time shall not exceed one minute, and not more than 25% of indicator flag shall be burned or charred. No dripping or flowing.	RW-2500 Section 4.3.15.3
Fungus Resistance		Rating of 1 or less	ASTM G 21
Water Absorption 24 hours at 23°C (73°F)	%	0.5 maximum	ASTM D 570